

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1249670

Luminaire Tested: P3AS17R359027DE010 E3DLP1H

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1249670
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-17)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R359027DE010 E3DLP1H
Description: 3in Adjustable LED luminaire with, R35 optic, 2700K CCT AND, 90CRI , E3DLP1H TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 780.0 lumens
Efficiency: N/A
Efficacy: 36.8 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.72
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1249670
CATALOG NUMBER: P3AS17R359027DE010 E3DLP1H

Luminous Intensity Polar Plot





TEST NUMBER: P1249670
 CATALOG NUMBER: P3AS17R359027DE010 E3DLP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	95	95	95	93
2	107	102	98	94	105	100	97	93	97	94	91	94	92	89	91	89	87	87	87	87	86
3	102	95	90	86	100	94	89	85	91	87	84	89	85	82	86	84	81	81	81	81	80
4	97	89	83	79	95	88	82	78	86	81	77	84	80	77	82	78	76	76	76	76	74
5	92	83	77	73	90	82	77	73	81	76	72	79	75	71	77	74	71	71	71	71	69
6	87	78	72	68	86	77	72	68	76	71	67	75	70	67	73	69	66	66	66	66	65
7	83	74	68	63	82	73	67	63	72	67	63	71	66	63	69	65	62	62	62	62	61
8	79	70	64	60	78	69	63	59	68	63	59	67	62	59	66	62	59	59	59	59	57
9	76	66	60	56	75	66	60	56	65	59	56	64	59	56	63	59	56	56	56	56	54
10	72	63	57	53	71	62	57	53	61	56	53	61	56	53	60	56	53	53	53	53	51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	250704
5°	244529
10°	223554
15°	189763
20°	150210
25°	113619
30°	82722
35°	55948
40°	34379
45°	19754
50°	11872
55°	9634
60°	8420
65°	7472
70°	6155
75°	6100
80°	6061
85°	6038

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 19754 cd/sqm



TEST NUMBER: P1249670
 CATALOG NUMBER: P3AS17R359027DE010 E3DLP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	102.7	13.2
10°-20°	230.4	29.5
20°-30°	215.6	27.6
30°-40°	131.9	16.9
40°-50°	52.0	6.7
50°-60°	22.9	2.9
60°-70°	14.2	1.8
70°-80°	7.6	1.0
80°-90°	2.6	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	548.7	70.3
0°-40°	680.6	87.3
0°-60°	755.5	96.9
0°-90°	780.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	780.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1143	
5°	1111	103
15°	836	230
25°	470	216
35°	209	132
45°	64	52
55°	25	23
65°	14	14
75°	7	8
85°	2	3
90°	0	



TEST NUMBER: P1249670
CATALOG NUMBER: P3AS17R359027DE010 E3DLP1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	1143.3
1°	1144.5
2°	1140.9
3°	1133.7
4°	1122.9
5°	1110.9
6°	1095.3
7°	1077.3
8°	1055.7
9°	1031.7
10°	1004.0
11°	975.2
12°	944.0
13°	910.4
14°	873.1
15°	835.9
17.5°	739.8
20°	643.7
22.5°	551.3
25°	469.6
27.5°	393.9
30°	326.7
32.5°	264.2
35°	209.0
37.5°	159.7
40°	120.1
42.5°	86.5
45°	63.7
47.5°	45.6
50°	34.8
52.5°	28.8
55°	25.2
57.5°	21.6
60°	19.2
62.5°	16.8
65°	14.4
67.5°	12.0
70°	9.6
72.5°	8.4
75°	7.2
77.5°	6.0
80°	4.8
82.5°	3.6
85°	2.4
87.5°	1.2



TEST NUMBER: P1249670
CATALOG NUMBER: P3AS17R359027DE010 E3DLP1H

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)