

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1248378

Luminaire Tested: P3AS05R159027DE010 E3D1WH

Issue Date: 1/29/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1248378  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-7)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS05R159027DE010 E3D1WH  
Description: 3in Adjustable LED luminaire with, R15 optic, 2700K CCT AND, 90CRI , E3D1WH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 604.0 lumens  
Efficiency: N/A  
Efficacy: 83.9 lumens/watt  
Spacing Criteria (0/90/45): 0.3 / 0.3 / 0.29  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 7.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1248378

CATALOG NUMBER: P3AS05R159027DE010 E3D1WH

### Luminous Intensity Polar Plot





TEST NUMBER: P1248378

CATALOG NUMBER: P3AS05R159027DE010 E3D1WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |     |     |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |     |     |     |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |     |     | 0   |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  | 0   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |     |     |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 | 102 | 102 | 100 |
| 1   | 116 | 114 | 112 | 111 | 113 | 112 | 110 | 109 | 108 | 107 | 105 |  | 104 | 103 | 102 |  | 101 | 100 | 99  | 98  |
| 2   | 112 | 109 | 107 | 105 | 110 | 108 | 105 | 103 | 105 | 103 | 101 |  | 102 | 100 | 99  |  | 99  | 98  | 97  | 96  |
| 3   | 110 | 106 | 102 | 100 | 108 | 104 | 102 | 99  | 102 | 100 | 98  |  | 100 | 98  | 96  |  | 98  | 96  | 95  | 94  |
| 4   | 107 | 102 | 99  | 96  | 106 | 101 | 98  | 96  | 99  | 97  | 95  |  | 98  | 96  | 94  |  | 96  | 94  | 93  | 92  |
| 5   | 105 | 100 | 96  | 94  | 103 | 99  | 96  | 93  | 97  | 94  | 92  |  | 96  | 93  | 92  |  | 94  | 93  | 91  | 90  |
| 6   | 102 | 97  | 94  | 91  | 101 | 96  | 93  | 91  | 95  | 92  | 90  |  | 94  | 92  | 90  |  | 93  | 91  | 89  | 88  |
| 7   | 100 | 95  | 91  | 89  | 99  | 94  | 91  | 89  | 93  | 90  | 88  |  | 92  | 90  | 88  |  | 91  | 89  | 88  | 87  |
| 8   | 98  | 93  | 89  | 87  | 97  | 92  | 89  | 87  | 91  | 89  | 87  |  | 91  | 88  | 86  |  | 90  | 88  | 86  | 85  |
| 9   | 96  | 91  | 88  | 85  | 96  | 91  | 87  | 85  | 90  | 87  | 85  |  | 89  | 87  | 85  |  | 89  | 86  | 85  | 84  |
| 10  | 95  | 89  | 86  | 84  | 94  | 89  | 86  | 84  | 88  | 85  | 83  |  | 88  | 85  | 83  |  | 87  | 85  | 83  | 82  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |         |
|-----|---------|
|     | 0°      |
| 0°  | 1150171 |
| 5°  | 937880  |
| 10° | 459332  |
| 15° | 140591  |
| 20° | 59529   |
| 25° | 26929   |
| 30° | 10508   |
| 35° | 4845    |
| 40° | 1517    |
| 45° | 558     |
| 50° | 239     |
| 55° | 76      |
| 60° | 88      |
| 65° | 104     |
| 70° | 0       |
| 75° | 0       |
| 80° | 0       |
| 85° | 0       |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 558 cd/sqm

TEST NUMBER: P1248378

CATALOG NUMBER: P3AS05R159027DE010 E3D1WH

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 331.7  | 54.9      |
| 10°-20°   | 203.5  | 33.7      |
| 20°-30°   | 54.7   | 9.1       |
| 30°-40°   | 12.0   | 2.0       |
| 40°-50°   | 1.7    | 0.3       |
| 50°-60°   | 0.3    | 0.0       |
| 60°-70°   | 0.1    | 0.0       |
| 70°-80°   | 0.0    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 589.8  | 97.7      |
| 0°-40°    | 601.9  | 99.7      |
| 0°-60°    | 603.9  | 100.0     |
| 0°-90°    | 604.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 604.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 5245 |      |
| 5°  | 4261 | 332  |
| 15° | 619  | 204  |
| 25° | 111  | 55   |
| 35° | 18   | 12   |
| 45° | 2    | 2    |
| 55° | 0    | 0    |
| 65° | 0    | 0    |
| 75° | 0    | 0    |
| 85° | 0    | 0    |
| 90° | 0    |      |

TEST NUMBER: P1248378

CATALOG NUMBER: P3AS05R159027DE010 E3D1WH

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 5245.2 |
| 1°    | 5212.5 |
| 2°    | 5107.3 |
| 3°    | 4917.9 |
| 4°    | 4632.8 |
| 5°    | 4260.8 |
| 6°    | 3840.1 |
| 7°    | 3371.5 |
| 8°    | 2941.0 |
| 9°    | 2484.5 |
| 10°   | 2062.9 |
| 11°   | 1645.6 |
| 12°   | 1266.1 |
| 13°   | 973.8  |
| 14°   | 770.9  |
| 15°   | 619.3  |
| 17.5° | 383.9  |
| 20°   | 255.1  |
| 22.5° | 171.8  |
| 25°   | 111.3  |
| 27.5° | 66.0   |
| 30°   | 41.5   |
| 32.5° | 27.9   |
| 35°   | 18.1   |
| 37.5° | 10.1   |
| 40°   | 5.3    |
| 42.5° | 3.0    |
| 45°   | 1.8    |
| 47.5° | 1.1    |
| 50°   | 0.7    |
| 52.5° | 0.5    |
| 55°   | 0.2    |
| 57.5° | 0.2    |
| 60°   | 0.2    |
| 62.5° | 0.2    |
| 65°   | 0.2    |
| 67.5° | 0.0    |
| 70°   | 0.0    |
| 72.5° | 0.0    |
| 75°   | 0.0    |
| 77.5° | 0.0    |
| 80°   | 0.0    |
| 82.5° | 0.0    |
| 85°   | 0.0    |
| 87.5° | 0.0    |



TEST NUMBER: P1248378

CATALOG NUMBER: P3AS05R159027DE010 E3D1WH

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)