

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1249696

Luminaire Tested: P3AS17R409027DE010 E3DLD1H

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1249696
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-22)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R409027DE010 E3DLD1H
Description: 3in Adjustable LED luminaire with, R40 optic, 2700K CCT AND, 90CRI , E3DLD1H TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1074.0 lumens
Efficiency: N/A
Efficacy: 50.7 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1249696
CATALOG NUMBER: P3AS17R409027DE010 E3DLD1H

Luminous Intensity Polar Plot





TEST NUMBER: P1249696
 CATALOG NUMBER: P3AS17R409027DE010 E3DLD1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91			
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76			
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69			
5	89	79	73	68	87	78	72	67	76	71	67	75	70	66	73	69	66	64			
6	84	74	67	62	82	73	67	62	71	66	61	70	65	61	68	64	61	59			
7	79	69	62	57	78	68	62	57	67	61	57	65	60	57	64	60	56	55			
8	75	64	58	53	74	64	58	53	63	57	53	62	56	53	61	56	52	51			
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48			
10	67	57	51	46	66	56	50	46	56	50	46	55	50	46	54	49	46	45			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	241099
5°	236715
10°	223131
15°	202680
20°	178049
25°	152041
30°	125969
35°	97146
40°	69130
45°	46578
50°	25415
55°	17930
60°	16885
65°	15566
70°	13848
75°	13217
80°	10607
85°	9057

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 46578 cd/sqm



TEST NUMBER: P1249696
 CATALOG NUMBER: P3AS17R409027DE010 E3DLD1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	100.3	9.3
10°-20°	248.7	23.2
20°-30°	287.5	26.8
30°-40°	226.6	21.1
40°-50°	116.3	10.8
50°-60°	44.5	4.1
60°-70°	29.4	2.7
70°-80°	16.0	1.5
80°-90°	4.7	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	636.5	59.3
0°-40°	863.1	80.4
0°-60°	1023.9	95.3
0°-90°	1074.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1074.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1100	
5°	1075	100
15°	893	249
25°	628	287
35°	363	227
45°	150	116
55°	47	44
65°	30	29
75°	16	16
85°	4	5
90°	0	



TEST NUMBER: P1249696
CATALOG NUMBER: P3AS17R409027DE010 E3DLD1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	1099.5
2.5°	1093.5
5°	1075.4
7.5°	1044.2
10°	1002.1
12.5°	952.9
15°	892.8
17.5°	830.3
20°	763.0
22.5°	694.5
25°	628.4
27.5°	562.3
30°	497.5
32.5°	431.4
35°	362.9
37.5°	299.2
40°	241.5
42.5°	192.3
45°	150.2
47.5°	109.3
50°	74.5
52.5°	54.1
55°	46.9
57.5°	42.1
60°	38.5
62.5°	33.6
65°	30.0
67.5°	25.2
70°	21.6
72.5°	18.0
75°	15.6
77.5°	12.0
80°	8.4
82.5°	7.2
85°	3.6
87.5°	2.4
90°	0.0

(END OF REPORT)