

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1248380

Luminaire Tested: P3AS05R159027DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1248380
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-3)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R159027DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R15 optic, 2700K CCT AND, 90CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 238.0 lumens
Efficiency: N/A
Efficacy: 33.1 lumens/watt
Spacing Criteria (0/90/45): 0.4 / 0.4 / 0.43
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1248380

CATALOG NUMBER: P3AS05R159027DE010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1248380

CATALOG NUMBER: P3AS05R159027DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99
2	110	106	103	100	108	104	101	99	101	99	97		98	96	95		96
3	106	101	97	93	104	99	96	93	97	94	91		94	92	90		92
4	102	96	92	88	100	95	91	88	93	89	87		91	88	86		89
5	98	92	87	84	97	91	87	83	89	85	83		88	84	82		86
6	95	88	83	80	94	87	83	80	86	82	79		85	81	79		83
7	92	85	80	77	91	84	80	76	83	79	76		82	78	76		81
8	89	81	77	74	88	81	77	73	80	76	73		79	75	73		78
9	86	79	74	71	85	78	74	71	77	73	71		77	73	70		76
10	84	76	71	68	83	76	71	68	75	71	68		74	71	68		74

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	203317
5°	180475
10°	125337
15°	74121
20°	42214
25°	24122
30°	13344
35°	7121
40°	3950
45°	2140
50°	1330
55°	1070
60°	921
65°	830
70°	705
75°	763
80°	631
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2140 cd/sqm

TEST NUMBER: P1248380

CATALOG NUMBER: P3AS05R159027DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	69.7	29.3
10°-20°	92.0	38.7
20°-30°	47.4	19.9
30°-40°	17.8	7.5
40°-50°	5.8	2.4
50°-60°	2.5	1.1
60°-70°	1.6	0.7
70°-80°	0.9	0.4
80°-90°	0.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	209.1	87.9
0°-40°	226.9	95.3
0°-60°	235.2	98.8
0°-90°	238.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	238.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	927	
5°	820	70
15°	326	92
25°	100	47
35°	27	18
45°	7	6
55°	3	3
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1248380

CATALOG NUMBER: P3AS05R159027DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	927.2
1°	925.4
2°	913.2
3°	890.0
4°	859.6
5°	819.9
6°	774.9
7°	725.7
8°	670.9
9°	616.7
10°	562.9
12.5°	433.1
15°	326.5
17.5°	244.4
20°	180.9
22.5°	135.0
25°	99.7
27.5°	72.7
30°	52.7
32.5°	37.4
35°	26.6
37.5°	19.0
40°	13.8
42.5°	9.9
45°	6.9
47.5°	5.0
50°	3.9
52.5°	3.2
55°	2.8
57.5°	2.3
60°	2.1
62.5°	1.8
65°	1.6
67.5°	1.4
70°	1.1
72.5°	1.1
75°	0.9
77.5°	0.7
80°	0.5
82.5°	0.5
85°	0.2
87.5°	0.0
90°	0.0

(END OF REPORT)