

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1249705

Luminaire Tested: P3AS17R409027DE010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1249705
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-23)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R409027DE010 E3DLP1WH
Description: 3in Adjustable LED luminaire with, R40 optic, 2700K CCT AND, 90CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1399.9 lumens
Efficiency: N/A
Efficacy: 66.0 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 0.65 / 0.63
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1249705

CATALOG NUMBER: P3AS17R409027DE010 E3DLP1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1249705

CATALOG NUMBER: P3AS17R409027DE010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	111	109	107	112	109	107	105	105	104	102	102	100	99	98	97	96	94		
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	92	91	89		
3	104	99	94	91	102	97	93	90	95	91	88	92	89	87	90	88	86	84		
4	100	93	88	85	98	92	88	84	90	86	83	88	85	82	86	84	81	80		
5	96	88	83	79	94	88	83	79	86	82	78	84	81	78	83	80	77	76		
6	92	84	79	75	91	83	78	75	82	78	74	81	77	74	79	76	73	72		
7	88	80	75	71	87	79	74	71	78	74	71	77	73	70	76	73	70	69		
8	85	76	71	68	84	76	71	67	75	70	67	74	70	67	73	69	67	65		
9	82	73	68	64	81	73	68	64	72	67	64	71	67	64	70	66	64	63		
10	78	70	65	62	78	70	65	61	69	64	61	68	64	61	67	64	61	60		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	619490
5°	601495
10°	545837
15°	450922
20°	325272
25°	201181
30°	108928
35°	56296
40°	30600
45°	17149
50°	8597
55°	6423
60°	5789
65°	5604
70°	5386
75°	5083
80°	4546
85°	3019

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 17149 cd/sqm

TEST NUMBER: P1249705

CATALOG NUMBER: P3AS17R409027DE010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	251.9	18.0
10°-20°	540.9	38.6
20°-30°	386.0	27.6
30°-40°	142.1	10.1
40°-50°	44.8	3.2
50°-60°	15.5	1.1
60°-70°	10.7	0.8
70°-80°	6.3	0.5
80°-90°	1.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1178.7	84.2
0°-40°	1320.8	94.3
0°-60°	1381.1	98.7
0°-90°	1399.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1399.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2825	
5°	2733	252
15°	1986	541
25°	832	386
35°	210	142
45°	55	45
55°	17	16
65°	11	11
75°	6	6
85°	1	2
90°	0	

TEST NUMBER: P1249705

CATALOG NUMBER: P3AS17R409027DE010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	2825.1
2.5°	2803.5
5°	2732.6
7.5°	2614.8
10°	2451.4
12.5°	2243.5
15°	1986.3
17.5°	1697.9
20°	1393.9
22.5°	1094.7
25°	831.5
27.5°	610.4
30°	430.2
32.5°	301.6
35°	210.3
37.5°	149.0
40°	106.9
42.5°	76.9
45°	55.3
47.5°	37.3
50°	25.2
52.5°	18.0
55°	16.8
57.5°	15.6
60°	13.2
62.5°	12.0
65°	10.8
67.5°	9.6
70°	8.4
72.5°	7.2
75°	6.0
77.5°	4.8
80°	3.6
82.5°	2.4
85°	1.2
87.5°	1.2
90°	0.0

(END OF REPORT)