

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1249718

Luminaire Tested: P3AS17R459027DE010 E3DL1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1249718
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-25)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R459027DE010 E3DL1WH
Description: 3in Adjustable LED luminaire with, R45 optic, 2700K CCT AND, 90CRI , E3DL1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 867.0 lumens
Efficiency: N/A
Efficacy: 40.9 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.76
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1249718

CATALOG NUMBER: P3AS17R459027DE010 E3DL1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1249718

CATALOG NUMBER: P3AS17R459027DE010 E3DL1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93		
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	86		
3	102	95	90	85	100	93	89	85	91	87	83	88	85	82	86	83	81	79		
4	96	88	83	78	94	87	82	78	85	81	77	83	79	76	81	78	75	74		
5	91	83	77	72	90	82	76	72	80	75	71	78	74	71	77	73	70	69		
6	87	78	72	67	85	77	71	67	75	70	66	74	69	66	73	69	66	64		
7	83	73	67	63	81	72	67	63	71	66	62	70	65	62	69	65	61	60		
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	56		
9	75	65	59	55	74	65	59	55	64	59	55	63	58	55	62	58	55	53		
10	72	62	56	52	71	61	56	52	61	55	52	60	55	52	59	55	52	50		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	258247
5°	252344
10°	232795
15°	202430
20°	166288
25°	129395
30°	95534
35°	67244
40°	41964
45°	22731
50°	12315
55°	10552
60°	9473
65°	8094
70°	6924
75°	7117
80°	6061
85°	6038

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 22731 cd/sqm

TEST NUMBER: P1249718

CATALOG NUMBER: P3AS17R459027DE010 E3DL1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	106.2	12.2
10°-20°	246.5	28.4
20°-30°	244.7	28.2
30°-40°	157.6	18.2
40°-50°	60.7	7.0
50°-60°	24.7	2.8
60°-70°	15.6	1.8
70°-80°	8.4	1.0
80°-90°	2.6	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	597.4	68.9
0°-40°	755.0	87.1
0°-60°	840.4	96.9
0°-90°	867.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	867.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1178	
5°	1146	106
15°	892	247
25°	535	245
35°	251	158
45°	73	61
55°	28	25
65°	16	16
75°	8	8
85°	2	3
90°	0	

TEST NUMBER: P1249718

CATALOG NUMBER: P3AS17R459027DE010 E3DL1WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1177.7
2.5°	1171.7
5°	1146.4
7.5°	1103.2
10°	1045.5
12.5°	973.4
15°	891.7
17.5°	802.8
20°	712.6
22.5°	621.3
25°	534.8
27.5°	453.1
30°	377.3
32.5°	311.2
35°	251.2
37.5°	197.1
40°	146.6
42.5°	105.8
45°	73.3
47.5°	49.3
50°	36.1
52.5°	30.0
55°	27.6
57.5°	24.0
60°	21.6
62.5°	18.0
65°	15.6
67.5°	13.2
70°	10.8
72.5°	9.6
75°	8.4
77.5°	6.0
80°	4.8
82.5°	3.6
85°	2.4
87.5°	1.2
90°	0.0

(END OF REPORT)