

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1248413

Luminaire Tested: P3AS05R209027DE010 E3DL1H

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1248413  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-7)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS05R209027DE010 E3DL1H  
Description: 3in Adjustable LED luminaire with, R20 optic, 2700K CCT AND, 90CRI , E3DL1H TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 484.0 lumens  
Efficiency: N/A  
Efficacy: 67.2 lumens/watt  
Spacing Criteria (0/90/45): 0.44 / 0.44 / 0.46  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 7.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1248413  
CATALOG NUMBER: P3AS05R209027DE010 E3DL1H

### Luminous Intensity Polar Plot





TEST NUMBER: P1248413  
 CATALOG NUMBER: P3AS05R209027DE010 E3DL1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20		
RC	80				70				50				30				10		0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10		0
RCR																			
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102		100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97		95
2	110	106	102	100	108	104	101	98	101	98	96	98	96	94	95	94	92		91
3	106	100	96	93	104	99	95	92	97	93	91	94	92	89	92	90	88		87
4	102	96	91	88	100	95	90	87	92	89	86	91	88	85	89	86	84		83
5	98	91	87	83	97	90	86	83	89	85	82	87	84	81	86	83	81		79
6	95	87	83	79	93	87	82	79	85	81	78	84	81	78	83	80	77		76
7	91	84	79	76	90	83	79	76	82	78	75	81	78	75	80	77	75		73
8	88	81	76	73	87	80	76	73	79	75	72	78	75	72	78	74	72		71
9	85	78	73	70	85	77	73	70	77	73	70	76	72	69	75	72	69		68
10	83	75	71	68	82	75	70	67	74	70	67	73	70	67	73	69	67		66

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	372382
5°	338498
10°	250185
15°	154757
20°	88371
25°	50446
30°	28283
35°	15392
40°	8444
45°	4652
50°	2695
55°	1950
60°	1842
65°	1712
70°	1475
75°	1610
80°	1137
85°	1258

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 4652 cd/sqm



TEST NUMBER: P1248413  
 CATALOG NUMBER: P3AS05R209027DE010 E3DL1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	133.2	27.5
10°-20°	190.1	39.3
20°-30°	99.2	20.5
30°-40°	38.4	7.9
40°-50°	12.5	2.6
50°-60°	4.9	1.0
60°-70°	3.2	0.7
70°-80°	1.9	0.4
80°-90°	0.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	422.5	87.3
0°-40°	460.8	95.2
0°-60°	478.2	98.8
0°-90°	484.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	484.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1698	
5°	1538	133
15°	682	190
25°	208	99
35°	58	38
45°	15	12
55°	5	5
65°	3	3
75°	2	2
85°	0	1
90°	0	



TEST NUMBER: P1248413  
CATALOG NUMBER: P3AS05R209027DE010 E3DL1H

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1698.2
1°	1694.9
2°	1674.8
3°	1644.0
4°	1596.3
5°	1537.8
6°	1468.6
7°	1391.9
8°	1303.1
9°	1216.6
10°	1123.6
12.5°	893.1
15°	681.7
17.5°	510.1
20°	378.7
22.5°	280.5
25°	208.5
27.5°	153.8
30°	111.7
32.5°	80.9
35°	57.5
37.5°	41.6
40°	29.5
42.5°	21.0
45°	15.0
47.5°	10.8
50°	7.9
52.5°	6.1
55°	5.1
57.5°	4.7
60°	4.2
62.5°	3.7
65°	3.3
67.5°	2.8
70°	2.3
72.5°	2.3
75°	1.9
77.5°	1.4
80°	0.9
82.5°	0.9
85°	0.5
87.5°	0.5
90°	0.0

(END OF REPORT)