

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1248417

Luminaire Tested: P3AS05R209027DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1248417
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-6)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R209027DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R20 optic, 2700K CCT AND, 90CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 180.0 lumens
Efficiency: N/A
Efficacy: 25.0 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1248417

CATALOG NUMBER: P3AS05R209027DE010 E3DLD1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1248417

CATALOG NUMBER: P3AS05R209027DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	109	106	104	110	107	105	102	103	101	99		99	98	96		96
2	106	100	96	92	104	99	94	91	95	92	89		92	89	87		90
3	100	93	87	82	98	91	86	82	88	84	80		86	82	79		84
4	94	86	79	75	92	85	79	74	82	77	73		80	76	72		78
5	89	80	73	68	87	79	73	68	77	71	67		75	70	67		73
6	84	74	68	63	82	73	67	63	72	66	62		70	65	62		69
7	80	69	63	58	78	69	62	58	67	62	58		66	61	57		65
8	75	65	59	54	74	64	58	54	63	58	54		62	57	53		61
9	72	61	55	50	70	61	55	50	60	54	50		59	54	50		58
10	68	58	51	47	67	57	51	47	56	51	47		56	50	47		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	44514
5°	43341
10°	39857
15°	35097
20°	30103
25°	25284
30°	20434
35°	15553
40°	11049
45°	7319
50°	4537
55°	2982
60°	2719
65°	2491
70°	2372
75°	2118
80°	2020
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 7319 cd/sqm

TEST NUMBER: P1248417

CATALOG NUMBER: P3AS05R209027DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	18.2	10.1
10°-20°	43.0	23.9
20°-30°	47.8	26.5
30°-40°	36.4	20.2
40°-50°	18.7	10.4
50°-60°	7.7	4.3
60°-70°	4.8	2.7
70°-80°	2.7	1.5
80°-90°	0.8	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	109.0	60.6
0°-40°	145.4	80.8
0°-60°	171.8	95.4
0°-90°	180.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	180.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	203	
5°	197	18
15°	155	43
25°	104	48
35°	58	36
45°	24	19
55°	8	8
65°	5	5
75°	2	3
85°	1	1
90°	0	

TEST NUMBER: P1248417

CATALOG NUMBER: P3AS05R209027DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	203.0
1°	203.3
2°	202.4
3°	201.2
4°	199.4
5°	196.9
6°	193.9
7°	190.7
8°	187.3
9°	183.1
10°	179.0
12.5°	167.1
15°	154.6
17.5°	141.8
20°	129.0
22.5°	116.2
25°	104.5
27.5°	92.8
30°	80.7
32.5°	69.3
35°	58.1
37.5°	48.2
40°	38.6
42.5°	30.4
45°	23.6
47.5°	17.8
50°	13.3
52.5°	9.8
55°	7.8
57.5°	7.1
60°	6.2
62.5°	5.5
65°	4.8
67.5°	4.1
70°	3.7
72.5°	3.0
75°	2.5
77.5°	2.1
80°	1.6
82.5°	1.1
85°	0.7
87.5°	0.2
90°	0.0

(END OF REPORT)