

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1248421

Luminaire Tested: P3AS05R209027DE010 E3DLD1WH

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1248421  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-6)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS05R209027DE010 E3DLD1WH  
Description: 3in Adjustable LED luminaire with, R20 optic, 2700K CCT AND, 90CRI , E3DLD1WH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 368.0 lumens  
Efficiency: N/A  
Efficacy: 51.1 lumens/watt  
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.83  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 7.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1248421  
CATALOG NUMBER: P3AS05R209027DE010 E3DLD1WH

### Luminous Intensity Polar Plot





TEST NUMBER: P1248421  
 CATALOG NUMBER: P3AS05R209027DE010 E3DLD1WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	109	106	104	110	107	105	102	103	101	99	99	98	96	96	95	93	91				91
2	106	100	96	92	104	99	94	91	95	92	89	92	89	87	90	87	85	83				83
3	100	93	87	82	98	91	86	82	88	84	80	86	82	79	84	81	78	76				76
4	94	86	79	75	92	85	79	74	82	77	73	80	76	72	78	75	72	70				70
5	89	80	73	68	87	79	73	68	77	71	67	75	70	67	73	69	66	65				65
6	84	74	68	63	82	73	67	63	72	66	62	70	65	62	69	65	61	60				60
7	80	69	63	58	78	69	62	58	67	62	58	66	61	57	65	60	57	55				55
8	75	65	59	54	74	64	58	54	63	58	54	62	57	53	61	57	53	52				52
9	72	61	55	50	70	61	55	50	60	54	50	59	54	50	58	53	50	48				48
10	68	58	51	47	67	57	51	47	56	51	47	56	51	47	55	50	47	45				45

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	91023
5°	88598
10°	81495
15°	71737
20°	61512
25°	51680
30°	41779
35°	31775
40°	22614
45°	14916
50°	9245
55°	6079
60°	5526
65°	5085
70°	4809
75°	4321
80°	4167
85°	3522

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 14916 cd/sqm



TEST NUMBER: P1248421  
 CATALOG NUMBER: P3AS05R209027DE010 E3DLD1WH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	37.2	10.1
10°-20°	88.0	23.9
20°-30°	97.6	26.5
30°-40°	74.5	20.2
40°-50°	38.1	10.4
50°-60°	15.7	4.3
60°-70°	9.8	2.7
70°-80°	5.5	1.5
80°-90°	1.6	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	222.8	60.6
0°-40°	297.3	80.8
0°-60°	351.1	95.4
0°-90°	368.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	368.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	415	
5°	402	37
15°	316	88
25°	214	98
35°	119	74
45°	48	38
55°	16	16
65°	10	10
75°	5	5
85°	1	2
90°	0	



TEST NUMBER: P1248421  
CATALOG NUMBER: P3AS05R209027DE010 E3DLD1WH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	415.1
1°	415.6
2°	413.7
3°	411.4
4°	407.6
5°	402.5
6°	396.4
7°	389.9
8°	382.9
9°	374.4
10°	366.0
12.5°	341.7
15°	316.0
17.5°	289.8
20°	263.6
22.5°	237.5
25°	213.6
27.5°	189.8
30°	165.0
32.5°	141.6
35°	118.7
37.5°	98.6
40°	79.0
42.5°	62.2
45°	48.1
47.5°	36.5
50°	27.1
52.5°	20.1
55°	15.9
57.5°	14.5
60°	12.6
62.5°	11.2
65°	9.8
67.5°	8.4
70°	7.5
72.5°	6.1
75°	5.1
77.5°	4.2
80°	3.3
82.5°	2.3
85°	1.4
87.5°	0.5
90°	0.0

(END OF REPORT)