

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1249759

Luminaire Tested: P3AS17R509027DE010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1249759
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-31)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R509027DE010 E3DLP1WH
Description: 3in Adjustable LED luminaire with, R50 optic, 2700K CCT AND, 90CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1351.9 lumens
Efficiency: N/A
Efficacy: 63.8 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.75
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1249759

CATALOG NUMBER: P3AS17R509027DE010 E3DLP1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1249759

CATALOG NUMBER: P3AS17R509027DE010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10			0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102			100
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95			94
2	108	103	99	96	106	102	98	95	98	95	93	95	93	91	93	91	89			87
3	103	97	92	88	101	95	91	87	93	89	86	90	87	84	88	85	83			82
4	98	91	85	81	96	90	85	81	87	83	80	85	82	79	84	80	78			76
5	93	85	80	75	92	84	79	75	83	78	74	81	77	74	79	76	73			72
6	89	80	75	71	88	80	74	70	78	73	70	77	73	69	75	72	69			67
7	85	76	70	66	84	75	70	66	74	69	66	73	69	65	72	68	65			64
8	81	72	66	62	80	71	66	62	70	65	62	69	65	62	68	64	61			60
9	78	68	63	59	76	68	62	59	67	62	59	66	62	58	65	61	58			57
10	74	65	59	56	73	65	59	56	64	59	55	63	58	55	62	58	55			54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	430448
5°	421769
10°	395072
15°	353668
20°	297619
25°	227142
30°	147618
35°	87535
40°	50580
45°	25336
50°	9415
55°	7340
60°	6842
65°	6226
70°	6155
75°	6100
80°	6061
85°	6038

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 25336 cd/sqm

TEST NUMBER: P1249759

CATALOG NUMBER: P3AS17R509027DE010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	178.3	13.2
10°-20°	430.8	31.9
20°-30°	422.7	31.3
30°-40°	212.9	15.8
40°-50°	67.3	5.0
50°-60°	17.4	1.3
60°-70°	12.3	0.9
70°-80°	7.6	0.6
80°-90°	2.6	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1031.8	76.3
0°-40°	1244.7	92.1
0°-60°	1329.4	98.3
0°-90°	1351.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1351.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1963	
5°	1916	178
15°	1558	431
25°	939	423
35°	327	213
45°	82	67
55°	19	17
65°	12	12
75°	7	8
85°	2	3
90°	0	

TEST NUMBER: P1249759

CATALOG NUMBER: P3AS17R509027DE010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1963.0
2.5°	1951.0
5°	1916.1
7.5°	1853.6
10°	1774.3
12.5°	1672.1
15°	1557.9
17.5°	1425.7
20°	1275.4
22.5°	1113.1
25°	938.8
27.5°	753.7
30°	583.0
32.5°	438.8
35°	327.0
37.5°	241.6
40°	176.7
42.5°	125.0
45°	81.7
47.5°	46.9
50°	27.6
52.5°	20.4
55°	19.2
57.5°	16.8
60°	15.6
62.5°	14.4
65°	12.0
67.5°	10.8
70°	9.6
72.5°	8.4
75°	7.2
77.5°	6.0
80°	4.8
82.5°	3.6
85°	2.4
87.5°	1.2
90°	0.0

(END OF REPORT)