

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1248448

Luminaire Tested: P3AS05R259027DE010 E3DLD1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1248448
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-10)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R259027DE010 E3DLD1WH
Description: 3in Adjustable LED luminaire with, R25 optic, 2700K CCT AND, 90CRI , E3DLD1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 375.0 lumens
Efficiency: N/A
Efficacy: 52.1 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1248448
CATALOG NUMBER: P3AS05R259027DE010 E3DLD1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1248448
 CATALOG NUMBER: P3AS05R259027DE010 E3DLD1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	112	109	106	104	110	107	105	102	103	101	99	99	98	96	96	94	93	91				91
2	106	100	96	92	104	99	94	91	95	92	89	92	89	87	89	87	85	83				83
3	100	92	87	82	98	91	86	82	88	84	80	86	82	79	83	80	78	76				76
4	94	85	79	74	92	84	78	74	82	77	73	80	76	72	78	74	71	70				70
5	89	79	73	68	87	78	72	68	76	71	67	75	70	66	73	69	66	64				64
6	84	74	67	62	82	73	67	62	71	66	62	70	65	61	69	64	61	59				59
7	79	69	62	58	78	68	62	58	67	61	57	66	61	57	65	60	57	55				55
8	75	65	58	54	74	64	58	53	63	57	53	62	57	53	61	56	53	51				51
9	71	61	54	50	70	60	54	50	59	54	50	58	53	50	57	53	49	48				48
10	68	57	51	47	67	57	51	47	56	50	47	55	50	46	54	50	46	45				45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	89116
5°	86991
10°	80626
15°	71805
20°	61699
25°	52455
30°	43171
35°	33649
40°	24217
45°	15350
50°	9074
55°	6270
60°	5745
65°	5344
70°	4809
75°	4321
80°	4167
85°	3522

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 15350 cd/sqm



TEST NUMBER: P1248448
 CATALOG NUMBER: P3AS05R259027DE010 E3DLD1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	36.7	9.8
10°-20°	87.8	23.4
20°-30°	99.2	26.5
30°-40°	78.5	20.9
40°-50°	39.6	10.6
50°-60°	15.9	4.2
60°-70°	10.2	2.7
70°-80°	5.6	1.5
80°-90°	1.6	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	223.7	59.6
0°-40°	302.1	80.6
0°-60°	357.7	95.4
0°-90°	375.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	375.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	406	
5°	395	37
15°	316	88
25°	217	99
35°	126	78
45°	50	40
55°	16	16
65°	10	10
75°	5	6
85°	1	2
90°	0	



TEST NUMBER: P1248448
CATALOG NUMBER: P3AS05R259027DE010 E3DLD1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	406.4
1°	406.4
2°	405.0
3°	402.7
4°	399.4
5°	395.2
6°	390.1
7°	384.0
8°	377.5
9°	370.0
10°	362.1
11°	353.2
12°	344.8
13°	335.0
14°	325.6
15°	316.3
17.5°	290.1
20°	264.4
22.5°	240.1
25°	216.8
27.5°	193.9
30°	170.5
32.5°	148.6
35°	125.7
37.5°	104.6
40°	84.6
42.5°	65.9
45°	49.5
47.5°	36.9
50°	26.6
52.5°	20.1
55°	16.4
57.5°	14.9
60°	13.1
62.5°	11.7
65°	10.3
67.5°	8.9
70°	7.5
72.5°	6.5
75°	5.1
77.5°	4.2
80°	3.3
82.5°	2.3
85°	1.4
87.5°	0.5



TEST NUMBER: P1248448
CATALOG NUMBER: P3AS05R259027DE010 E3DLD1WH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)