

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1248450

Luminaire Tested: P3AS05R259027DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1248450
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R259027DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R25 optic, 2700K CCT AND, 90CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 147.0 lumens
Efficiency: N/A
Efficacy: 20.4 lumens/watt
Spacing Criteria (0/90/45): 0.62 / 0.62 / 0.68
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1248450

CATALOG NUMBER: P3AS05R259027DE010 E3DLP1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1248450

CATALOG NUMBER: P3AS05R259027DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	101		100	99	98		97
2	107	102	98	95	105	101	97	94	97	94	92		94	92	90		92
3	102	95	90	86	100	94	89	86	91	87	84		89	86	83		87
4	97	89	84	79	95	88	83	79	86	81	78		84	80	77		82
5	92	84	78	74	91	83	77	73	81	76	73		79	75	72		78
6	88	79	73	69	86	78	72	68	77	72	68		75	71	67		74
7	84	74	68	64	82	74	68	64	72	67	64		71	67	63		70
8	80	70	65	60	79	70	64	60	69	64	60		68	63	60		67
9	76	67	61	57	75	66	61	57	65	60	57		64	60	57		64
10	73	64	58	54	72	63	58	54	62	57	54		62	57	54		61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	53373
5°	51200
10°	44844
15°	36050
20°	27699
25°	20953
30°	15142
35°	10065
40°	6097
45°	3566
50°	2252
55°	1835
60°	1623
65°	1453
70°	1154
75°	1186
80°	884
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3566 cd/sqm

TEST NUMBER: P1248450

CATALOG NUMBER: P3AS05R259027DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	21.2	14.4
10°-20°	43.9	29.9
20°-30°	39.7	27.0
30°-40°	23.8	16.2
40°-50°	9.5	6.4
50°-60°	4.4	3.0
60°-70°	2.7	1.8
70°-80°	1.4	1.0
80°-90°	0.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	104.8	71.3
0°-40°	128.6	87.5
0°-60°	142.5	96.9
0°-90°	147.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	147.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	243	
5°	233	21
15°	159	44
25°	87	40
35°	38	24
45°	12	9
55°	5	4
65°	3	3
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1248450

CATALOG NUMBER: P3AS05R259027DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	243.4
1°	243.4
2°	242.2
3°	239.7
4°	236.5
5°	232.6
6°	227.6
7°	221.8
8°	215.2
9°	208.5
10°	201.4
11°	193.2
12°	184.7
13°	176.2
14°	167.8
15°	158.8
17.5°	137.7
20°	118.7
22.5°	101.5
25°	86.6
27.5°	72.6
30°	59.8
32.5°	48.1
35°	37.6
37.5°	28.6
40°	21.3
42.5°	15.6
45°	11.5
47.5°	8.7
50°	6.6
52.5°	5.5
55°	4.8
57.5°	4.1
60°	3.7
62.5°	3.0
65°	2.8
67.5°	2.3
70°	1.8
72.5°	1.6
75°	1.4
77.5°	1.1
80°	0.7
82.5°	0.5
85°	0.5
87.5°	0.2



TEST NUMBER: P1248450

CATALOG NUMBER: P3AS05R259027DE010 E3DLP1GPH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)