

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1248508

Luminaire Tested: P3AS05R359027DE010 E3DLD1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1248508
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-18)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R359027DE010 E3DLD1WH
Description: 3in Adjustable LED luminaire with, R35 optic, 2700K CCT AND, 90CRI , E3DLD1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 378.0 lumens
Efficiency: N/A
Efficacy: 52.5 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1248508
CATALOG NUMBER: P3AS05R359027DE010 E3DLD1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1248508
 CATALOG NUMBER: P3AS05R359027DE010 E3DLD1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91			91
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83			83
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76			76
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69			69
5	89	79	73	68	87	78	72	67	76	71	67	75	70	66	73	69	66	64			64
6	84	74	67	62	82	73	67	62	71	66	61	70	65	61	68	64	61	59			59
7	79	69	62	57	78	68	62	57	67	61	57	65	60	57	64	60	56	55			55
8	75	64	58	53	74	64	57	53	63	57	53	62	56	53	61	56	52	51			51
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48			48
10	67	57	51	46	66	56	50	46	56	50	46	55	50	46	54	49	46	45			45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	86353
5°	84525
10°	79157
15°	71056
20°	61792
25°	52672
30°	44108
35°	35148
40°	25419
45°	16064
50°	8767
55°	6079
60°	5745
65°	5344
70°	5065
75°	4321
80°	4167
85°	3522

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 16064 cd/sqm



TEST NUMBER: P1248508
 CATALOG NUMBER: P3AS05R359027DE010 E3DLD1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	35.7	9.5
10°-20°	87.1	23.0
20°-30°	99.8	26.4
30°-40°	81.5	21.5
40°-50°	41.1	10.9
50°-60°	15.3	4.0
60°-70°	10.2	2.7
70°-80°	5.6	1.5
80°-90°	1.7	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	222.6	58.9
0°-40°	304.1	80.4
0°-60°	360.4	95.3
0°-90°	378.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	378.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	394	
5°	384	36
15°	313	87
25°	218	100
35°	131	81
45°	52	41
55°	16	15
65°	10	10
75°	5	6
85°	1	2
90°	0	



TEST NUMBER: P1248508
CATALOG NUMBER: P3AS05R359027DE010 E3DLD1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	393.8
1°	393.3
2°	392.4
3°	390.5
4°	387.7
5°	384.0
6°	379.3
7°	374.6
8°	368.5
9°	362.5
10°	355.5
11°	348.0
12°	340.1
13°	331.2
14°	321.8
15°	313.0
17.5°	289.1
20°	264.8
22.5°	240.1
25°	217.7
27.5°	195.7
30°	174.2
32.5°	152.7
35°	131.3
37.5°	109.8
40°	88.8
42.5°	69.1
45°	51.8
47.5°	37.4
50°	25.7
52.5°	18.7
55°	15.9
57.5°	14.5
60°	13.1
62.5°	11.7
65°	10.3
67.5°	8.9
70°	7.9
72.5°	6.5
75°	5.1
77.5°	4.2
80°	3.3
82.5°	2.3
85°	1.4
87.5°	0.9



TEST NUMBER: P1248508
CATALOG NUMBER: P3AS05R359027DE010 E3DLD1WH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)