

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1248590

Luminaire Tested: P3AS05R509027DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1248590
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-30)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R509027DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R50 optic, 2700K CCT AND, 90CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 201.1 lumens
Efficiency: N/A
Efficacy: 27.9 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.93
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1248590

CATALOG NUMBER: P3AS05R509027DE010 E3DLD1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1248590

CATALOG NUMBER: P3AS05R509027DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	102	103	101	99		99	97	96		95
2	106	100	95	91	103	98	94	90	95	91	88		92	89	86		89
3	99	92	86	81	97	90	85	81	88	83	79		85	81	78		83
4	93	85	78	73	91	83	77	73	81	76	72		79	75	71		77
5	88	78	72	67	86	77	71	66	75	70	66		74	69	65		72
6	83	73	66	61	81	72	65	61	70	65	60		69	64	60		67
7	78	68	61	56	77	67	61	56	66	60	56		64	59	55		63
8	74	63	57	52	73	63	56	52	61	56	52		60	55	51		59
9	70	59	53	48	69	59	52	48	58	52	48		57	52	48		56
10	66	56	49	45	65	55	49	45	54	49	45		54	48	45		53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	40852
5°	40238
10°	38454
15°	35619
20°	32016
25°	28139
30°	23928
35°	19408
40°	14570
45°	9396
50°	4469
55°	3517
60°	3333
65°	3113
70°	2821
75°	2542
80°	2273
85°	2264

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9396 cd/sqm

TEST NUMBER: P1248590

CATALOG NUMBER: P3AS05R509027DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	17.1	8.5
10°-20°	43.7	21.8
20°-30°	53.1	26.4
30°-40°	45.1	22.4
40°-50°	23.4	11.6
50°-60°	8.5	4.2
60°-70°	5.9	2.9
70°-80°	3.2	1.6
80°-90°	1.0	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	114.0	56.7
0°-40°	159.1	79.1
0°-60°	191.0	95.0
0°-90°	201.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	201.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	186	
5°	183	17
15°	157	44
25°	116	53
35°	72	45
45°	30	23
55°	9	8
65°	6	6
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1248590

CATALOG NUMBER: P3AS05R509027DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	186.3
2.5°	185.6
5°	182.8
7.5°	178.7
10°	172.7
12.5°	165.2
15°	156.9
17.5°	147.5
20°	137.2
22.5°	126.6
25°	116.3
27.5°	105.5
30°	94.5
32.5°	83.5
35°	72.5
37.5°	61.7
40°	50.9
42.5°	40.6
45°	30.3
47.5°	20.2
50°	13.1
52.5°	10.1
55°	9.2
57.5°	8.3
60°	7.6
62.5°	6.7
65°	6.0
67.5°	5.0
70°	4.4
72.5°	3.7
75°	3.0
77.5°	2.3
80°	1.8
82.5°	1.4
85°	0.9
87.5°	0.5
90°	0.0

(END OF REPORT)