

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1249964

Luminaire Tested: P3AS20R309027D010 E3CB1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1249964
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-16)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R309027D010 E3CB1MMS
Description: 3in Adjustable LED luminaire with, R30 optic, 2700K CCT AND, 90CRI , E3CB1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2009.1 lumens
Efficiency: N/A
Efficacy: 69.8 lumens/watt
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.47
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1249964

CATALOG NUMBER: P3AS20R309027D010 E3CB1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1249964

CATALOG NUMBER: P3AS20R309027D010 E3CB1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	98
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97	96	95
2	111	108	105	102	109	106	104	101	103	101	99	100	99	97	98	96	95	94	93	92
3	108	103	100	97	106	102	99	96	100	97	95	97	95	93	95	94	92	91	90	89
4	105	100	96	93	103	99	95	92	97	94	91	95	92	90	93	91	89	88	87	86
5	102	96	92	89	100	95	91	89	94	90	88	92	89	87	91	88	87	85	84	83
6	99	93	89	86	98	92	88	86	91	88	85	90	87	85	89	86	84	83	82	81
7	96	90	86	83	95	89	86	83	88	85	82	87	84	82	86	84	82	81	80	79
8	94	87	83	81	93	87	83	80	86	83	80	85	82	80	84	82	80	79	78	77
9	91	85	81	78	90	84	81	78	84	80	78	83	80	78	82	79	77	76	75	74
10	89	83	79	76	88	82	78	76	82	78	76	81	78	76	80	77	75	74	73	72

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1636009
5°	1605081
10°	1420904
15°	900232
20°	341723
25°	101183
30°	39956
35°	12260
40°	5410
45°	1954
50°	1603
55°	1223
60°	1403
65°	1660
70°	1026
75°	1356
80°	2020
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 80°
Luminance: 2020 cd/sqm

TEST NUMBER: P1249964

CATALOG NUMBER: P3AS20R309027D010 E3CB1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	670.3	33.4
10°-20°	1044.7	52.0
20°-30°	242.6	12.1
30°-40°	37.6	1.9
40°-50°	6.4	0.3
50°-60°	3.0	0.2
60°-70°	2.6	0.1
70°-80°	1.7	0.1
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1957.6	97.4
0°-40°	1995.2	99.3
0°-60°	2004.6	99.8
0°-90°	2009.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2009.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7461	
5°	7292	670
15°	3966	1045
25°	418	243
35°	46	38
45°	6	6
55°	3	3
65°	3	3
75°	2	2
85°	0	0
90°	0	

TEST NUMBER: P1249964

CATALOG NUMBER: P3AS20R309027D010 E3CB1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	7460.8
1°	7456.0
2°	7435.5
3°	7400.8
4°	7356.6
5°	7291.9
6°	7211.4
7°	7091.5
8°	6927.4
9°	6686.0
10°	6381.4
11°	5988.5
12°	5545.1
13°	5052.7
14°	4511.5
15°	3965.5
17.5°	2594.2
20°	1464.4
22.5°	748.0
25°	418.2
27.5°	257.2
30°	157.8
32.5°	85.2
35°	45.8
37.5°	30.0
40°	18.9
42.5°	11.0
45°	6.3
47.5°	4.7
50°	4.7
52.5°	3.2
55°	3.2
57.5°	3.2
60°	3.2
62.5°	3.2
65°	3.2
67.5°	1.6
70°	1.6
72.5°	1.6
75°	1.6
77.5°	1.6
80°	1.6
82.5°	0.0
85°	0.0
87.5°	0.0



TEST NUMBER: P1249964

CATALOG NUMBER: P3AS20R309027D010 E3CB1MMS

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)