

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1248652

Luminaire Tested: P3AS05R609027DE010 E3DLD1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1248652
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-38)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R609027DE010 E3DLD1WH
Description: 3in Adjustable LED luminaire with, R60 optic, 2700K CCT AND, 90CRI , E3DLD1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 385.0 lumens
Efficiency: N/A
Efficacy: 53.5 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1248652
CATALOG NUMBER: P3AS05R609027DE010 E3DLD1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1248652
 CATALOG NUMBER: P3AS05R609027DE010 E3DLD1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	103	110	107	104	101	102	100	98	99	97	95	95	94	93	91			
2	105	99	94	90	103	98	93	89	94	90	87	91	88	85	88	86	84	82			
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	78	76	74			
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67			
5	87	77	70	65	85	76	69	65	74	68	64	72	67	63	71	66	63	61			
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56			
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51			
8	72	61	55	50	71	61	54	50	60	54	49	59	53	49	58	53	49	47			
9	68	57	51	46	67	57	50	46	56	50	46	55	49	46	54	49	45	44			
10	65	54	47	43	64	53	47	43	52	47	43	52	46	42	51	46	42	41			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	68350
5°	67576
10°	65240
15°	61635
20°	56798
25°	51438
30°	45678
35°	39030
40°	31030
45°	21894
50°	13066
55°	6614
60°	6359
65°	5811
70°	5386
75°	5168
80°	4672
85°	3522

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 21894 cd/sqm



TEST NUMBER: P1248652
 CATALOG NUMBER: P3AS05R609027DE010 E3DLD1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	28.8	7.5
10°-20°	75.9	19.7
20°-30°	97.4	25.3
30°-40°	90.3	23.5
40°-50°	55.0	14.3
50°-60°	18.3	4.8
60°-70°	11.1	2.9
70°-80°	6.3	1.6
80°-90°	1.8	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	202.1	52.5
0°-40°	292.5	76.0
0°-60°	365.8	95.0
0°-90°	385.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	385.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	312	
5°	307	29
15°	272	76
25°	213	97
35°	146	90
45°	71	55
55°	17	18
65°	11	11
75°	6	6
85°	1	2
90°	0	

TEST NUMBER: P1248652
CATALOG NUMBER: P3AS05R609027DE010 E3DLD1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	311.7
2.5°	310.3
5°	307.0
7.5°	300.9
10°	293.0
12.5°	283.2
15°	271.5
17.5°	257.9
20°	243.4
22.5°	228.0
25°	212.6
27.5°	196.7
30°	180.4
32.5°	164.0
35°	145.8
37.5°	126.6
40°	108.4
42.5°	89.2
45°	70.6
47.5°	54.7
50°	38.3
52.5°	22.9
55°	17.3
57.5°	15.9
60°	14.5
62.5°	12.6
65°	11.2
67.5°	9.8
70°	8.4
72.5°	7.0
75°	6.1
77.5°	4.7
80°	3.7
82.5°	2.3
85°	1.4
87.5°	0.9
90°	0.0

(END OF REPORT)