

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1249969

Luminaire Tested: P3AS20R309027D010 E3D1H

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1249969
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-10)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R309027D010 E3D1H
Description: 3in Adjustable LED luminaire with, R30 optic, 2700K CCT AND, 90CRI , E3D1H TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1992.0 lumens
Efficiency: N/A
Efficacy: 69.2 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.47
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1249969

CATALOG NUMBER: P3AS20R309027D010 E3D1H

Luminous Intensity Polar Plot





TEST NUMBER: P1249969

CATALOG NUMBER: P3AS20R309027D010 E3D1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97		
2	111	108	105	102	109	106	103	101	103	101	99	100	98	97	97	96	95	94		
3	108	103	100	97	106	102	99	96	99	97	95	97	95	93	95	93	92	90		
4	105	99	95	92	103	98	95	92	96	93	91	94	92	90	93	91	89	88		
5	101	96	92	89	100	95	91	88	93	90	87	92	89	87	90	88	86	85		
6	99	92	88	85	97	92	88	85	90	87	85	89	86	84	88	85	83	82		
7	96	89	85	82	95	89	85	82	88	84	82	87	84	81	86	83	81	80		
8	93	87	83	80	92	86	82	80	85	82	79	84	81	79	84	81	79	78		
9	91	84	80	77	90	84	80	77	83	79	77	82	79	77	82	79	77	76		
10	88	82	78	75	88	81	78	75	81	77	75	80	77	75	80	77	75	74		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1584895
5°	1564227
10°	1365706
15°	868064
20°	343917
25°	114878
30°	53451
35°	24226
40°	9303
45°	4559
50°	1330
55°	573
60°	351
65°	415
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4559 cd/sqm

TEST NUMBER: P1249969

CATALOG NUMBER: P3AS20R309027D010 E3D1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	649.7	32.6
10°-20°	1007.5	50.6
20°-30°	259.8	13.0
30°-40°	61.0	3.1
40°-50°	11.9	0.6
50°-60°	1.4	0.1
60°-70°	0.7	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1917.0	96.2
0°-40°	1978.1	99.3
0°-60°	1991.3	100.0
0°-90°	1992.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1992.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7228	
5°	7106	650
15°	3824	1008
25°	475	260
35°	90	61
45°	15	12
55°	2	1
65°	1	1
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1249969

CATALOG NUMBER: P3AS20R309027D010 E3D1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	7227.7
1°	7222.3
2°	7205.3
3°	7185.9
4°	7157.3
5°	7106.3
6°	7023.6
7°	6885.9
8°	6698.0
9°	6452.9
10°	6133.5
11°	5753.9
12°	5339.4
13°	4862.3
14°	4362.8
15°	3823.8
16°	3295.7
17°	2786.8
18°	2298.9
19°	1851.2
20°	1473.8
21°	1159.9
22°	912.5
23°	722.2
24°	578.4
25°	474.8
26°	395.9
27°	336.4
28°	290.7
29°	249.0
30°	211.1
32.5°	133.0
35°	90.5
37.5°	56.4
40°	32.5
42.5°	21.7
45°	14.7
47.5°	8.5
50°	3.9
52.5°	1.5
55°	1.5
57.5°	0.8
60°	0.8
62.5°	0.8
65°	0.8



TEST NUMBER: P1249969

CATALOG NUMBER: P3AS20R309027D010 E3D1H

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.8
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)