

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1248658

Luminaire Tested: P3AS05R609027DE010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1248658
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-39)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R609027DE010 E3DLP1WH
Description: 3in Adjustable LED luminaire with, R60 optic, 2700K CCT AND, 90CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 492.0 lumens
Efficiency: N/A
Efficacy: 68.3 lumens/watt
Spacing Criteria (0/90/45): 0.87 / 0.87 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1248658

CATALOG NUMBER: P3AS05R609027DE010 E3DLP1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1248658

CATALOG NUMBER: P3AS05R609027DE010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	95	89	85	99	93	88	84	91	86	83		88	85	82		86
4	96	88	82	78	94	87	81	77	85	80	76		83	79	75		81
5	91	82	76	71	89	81	75	71	79	74	70		78	73	70		76
6	86	77	70	66	84	76	70	66	74	69	65		73	68	65		72
7	82	72	66	61	80	71	65	61	70	65	61		69	64	60		68
8	77	68	61	57	76	67	61	57	66	60	57		65	60	56		64
9	74	64	57	53	72	63	57	53	62	57	53		61	56	53		60
10	70	60	54	50	69	60	54	50	59	53	50		58	53	50		57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	116175
5°	115078
10°	111733
15°	104677
20°	92641
25°	77496
30°	60744
35°	44062
40°	29312
45°	18265
50°	9893
55°	2867
60°	2675
65°	2439
70°	2372
75°	2372
80°	2399
85°	2264

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 18265 cd/sqm

TEST NUMBER: P1248658

CATALOG NUMBER: P3AS05R609027DE010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	49.2	10.0
10°-20°	127.9	26.0
20°-30°	145.8	29.6
30°-40°	103.4	21.0
40°-50°	46.9	9.5
50°-60°	10.0	2.0
60°-70°	4.8	1.0
70°-80°	3.0	0.6
80°-90°	1.0	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	323.0	65.6
0°-40°	426.4	86.7
0°-60°	483.2	98.2
0°-90°	492.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	492.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	530	
5°	523	49
15°	461	128
25°	320	146
35°	165	103
45°	59	47
55°	8	10
65°	5	5
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1248658

CATALOG NUMBER: P3AS05R609027DE010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	529.8
2.5°	527.9
5°	522.8
7.5°	513.9
10°	501.8
12.5°	484.5
15°	461.1
17.5°	431.6
20°	397.0
22.5°	359.6
25°	320.3
27.5°	280.1
30°	239.9
32.5°	201.5
35°	164.6
37.5°	131.9
40°	102.4
42.5°	77.6
45°	58.9
47.5°	44.0
50°	29.0
52.5°	13.6
55°	7.5
57.5°	6.5
60°	6.1
62.5°	5.6
65°	4.7
67.5°	4.2
70°	3.7
72.5°	3.3
75°	2.8
77.5°	2.3
80°	1.9
82.5°	1.4
85°	0.9
87.5°	0.5
90°	0.0

(END OF REPORT)