

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1248660

Luminaire Tested: P3AS05R659027DE010 E3CB1MB

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1248660
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-44)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R659027DE010 E3CB1MB
Description: 3in Adjustable LED luminaire with, R65 optic, 2700K CCT AND, 90CRI , E3CB1MB TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 578.0 lumens
Efficiency: N/A
Efficacy: 80.3 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.9
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1248660
CATALOG NUMBER: P3AS05R659027DE010 E3CB1MB

Luminous Intensity Polar Plot





TEST NUMBER: P1248660
 CATALOG NUMBER: P3AS05R659027DE010 E3CB1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	93	93	93	93
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	92	90	89	87	87	87	87
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	88	85	83	81	81	81	81
4	97	90	84	80	96	89	84	80	87	82	79	85	81	78	83	80	77	75	75	75	75
5	93	84	78	74	91	83	78	74	82	77	73	80	76	73	78	75	72	70	70	70	70
6	88	79	73	69	86	78	73	69	77	72	68	75	71	68	74	70	67	66	66	66	66
7	84	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	62	62	62	62
8	80	70	64	60	78	69	64	60	68	63	60	67	63	59	66	62	59	58	58	58	58
9	76	66	60	56	75	66	60	56	65	60	56	64	59	56	63	59	56	54	54	54	54
10	72	63	57	53	71	62	57	53	61	56	53	60	56	53	60	55	52	51	51	51	51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	141261
5°	132951
10°	131260
15°	128945
20°	121741
25°	112990
30°	87836
35°	50808
40°	20467
45°	9427
50°	3684
55°	1415
60°	1228
65°	1193
70°	1218
75°	1186
80°	1137
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 9427 cd/sqm



TEST NUMBER: P1248660
 CATALOG NUMBER: P3AS05R659027DE010 E3CB1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	57.4	9.9
10°-20°	158.6	27.4
20°-30°	207.6	35.9
30°-40°	120.3	20.8
40°-50°	25.7	4.5
50°-60°	4.2	0.7
60°-70°	2.3	0.4
70°-80°	1.3	0.2
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	423.6	73.3
0°-40°	543.9	94.1
0°-60°	573.8	99.3
0°-90°	578.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	578.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	644	
5°	604	57
15°	568	159
25°	467	208
35°	190	120
45°	30	26
55°	4	4
65°	2	2
75°	1	1
85°	0	1
90°	0	



TEST NUMBER: P1248660
CATALOG NUMBER: P3AS05R659027DE010 E3CB1MB

CANDELA DISTRIBUTION (FULL):

	0°
0°	644.2
2.5°	625.9
5°	604.0
7.5°	595.1
10°	589.5
12.5°	581.5
15°	568.0
17.5°	546.9
20°	521.7
22.5°	497.8
25°	467.0
27.5°	415.1
30°	346.9
32.5°	268.8
35°	189.8
37.5°	120.1
40°	71.5
42.5°	44.9
45°	30.4
47.5°	19.6
50°	10.8
52.5°	5.1
55°	3.7
57.5°	3.3
60°	2.8
62.5°	2.8
65°	2.3
67.5°	1.9
70°	1.9
72.5°	1.4
75°	1.4
77.5°	0.9
80°	0.9
82.5°	0.5
85°	0.5
87.5°	0.5
90°	0.0

(END OF REPORT)