

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1248677

Luminaire Tested: P3AS05R659027DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1248677
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-42)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R659027DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R65 optic, 2700K CCT AND, 90CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 180.0 lumens
Efficiency: N/A
Efficacy: 25.0 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1248677
CATALOG NUMBER: P3AS05R659027DE010 E3DLD1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1248677
 CATALOG NUMBER: P3AS05R659027DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	103	110	107	104	101	102	100	98	99	97	95	95	94	93	91			91
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	86	84	82			82
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	78	76	74			74
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67			67
5	87	77	70	65	85	76	69	65	74	68	64	72	67	63	71	66	63	61			61
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56			56
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51			51
8	72	61	55	50	71	61	54	50	60	54	49	59	53	49	58	53	49	47			47
9	68	57	51	46	67	57	50	46	56	50	46	55	49	46	54	49	45	44			44
10	65	54	47	43	64	53	47	43	52	47	43	52	46	42	51	46	42	41			41

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	32037
5°	31609
10°	30549
15°	28808
20°	26556
25°	24122
30°	21370
35°	18176
40°	14456
45°	10203
50°	5936
55°	3250
60°	3026
65°	2750
70°	2500
75°	2288
80°	2020
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 10203 cd/sqm



TEST NUMBER: P1248677
 CATALOG NUMBER: P3AS05R659027DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	13.5	7.5
10°-20°	35.5	19.7
20°-30°	45.6	25.3
30°-40°	42.2	23.4
40°-50°	25.5	14.1
50°-60°	8.7	4.8
60°-70°	5.2	2.9
70°-80°	2.9	1.6
80°-90°	0.8	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	94.6	52.6
0°-40°	136.8	76.0
0°-60°	171.0	95.0
0°-90°	180.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	180.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	146	
5°	144	14
15°	127	35
25°	100	46
35°	68	42
45°	33	25
55°	8	9
65°	5	5
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1248677
CATALOG NUMBER: P3AS05R659027DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	146.1
2.5°	145.4
5°	143.6
7.5°	140.8
10°	137.2
12.5°	132.6
15°	126.9
17.5°	120.7
20°	113.8
22.5°	106.8
25°	99.7
27.5°	92.1
30°	84.4
32.5°	76.6
35°	67.9
37.5°	59.4
40°	50.5
42.5°	41.6
45°	32.9
47.5°	24.9
50°	17.4
52.5°	11.0
55°	8.5
57.5°	7.5
60°	6.9
62.5°	5.9
65°	5.3
67.5°	4.6
70°	3.9
72.5°	3.4
75°	2.7
77.5°	2.3
80°	1.6
82.5°	1.1
85°	0.7
87.5°	0.5
90°	0.0

(END OF REPORT)