

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1250032

Luminaire Tested: P3AS20R409027D010 E3D1WH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1250032
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-12)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R409027D010 E3D1WH
Description: 3in Adjustable LED luminaire with, R40 optic, 2700K CCT AND, 90CRI , E3D1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2210.0 lumens
Efficiency: N/A
Efficacy: 76.7 lumens/watt
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.6
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1250032
CATALOG NUMBER: P3AS20R409027D010 E3D1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1250032
 CATALOG NUMBER: P3AS20R409027D010 E3D1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	115	112	110	109	112	110	109	107	106	105	104	103	102	101	99	98	98	96			
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	96	95	94	92			
3	107	102	98	95	105	100	97	94	98	95	93	96	93	91	93	91	90	88			
4	103	97	93	90	101	96	92	89	94	91	88	92	89	87	90	88	86	85			
5	99	93	89	85	98	92	88	85	91	87	84	89	86	84	88	85	83	82			
6	96	89	85	81	95	89	84	81	87	83	81	86	83	80	85	82	80	79			
7	93	86	81	78	92	85	81	78	84	80	77	83	80	77	82	79	77	76			
8	90	83	78	75	89	82	78	75	81	77	75	80	77	74	79	76	74	73			
9	87	80	75	72	86	79	75	72	78	75	72	78	74	72	77	74	71	70			
10	84	77	72	70	83	77	72	69	76	72	69	75	72	69	74	71	69	68			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1126489
5°	1118355
10°	1089091
15°	972855
20°	645059
25°	241659
30°	64643
35°	25270
40°	9074
45°	4311
50°	1330
55°	573
60°	351
65°	415
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 4311 cd/sqm



TEST NUMBER: P1250032
 CATALOG NUMBER: P3AS20R409027D010 E3D1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	479.5	21.7
10°-20°	1135.5	51.4
20°-30°	514.9	23.3
30°-40°	66.7	3.0
40°-50°	11.5	0.5
50°-60°	1.4	0.1
60°-70°	0.5	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2129.9	96.4
0°-40°	2196.6	99.4
0°-60°	2209.5	100.0
0°-90°	2210.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2210.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5137	
5°	5081	479
15°	4285	1135
25°	999	515
35°	94	67
45°	14	12
55°	2	1
65°	1	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1250032
CATALOG NUMBER: P3AS20R409027D010 E3D1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	5137.2
1°	5134.1
2°	5126.4
3°	5114.8
4°	5100.1
5°	5080.7
6°	5058.3
7°	5030.4
8°	4996.4
9°	4950.0
10°	4891.2
11°	4822.3
12°	4730.2
13°	4616.5
14°	4468.0
15°	4285.4
16°	4052.5
17°	3787.1
18°	3468.4
19°	3131.8
20°	2764.3
21°	2396.8
22°	2034.8
23°	1674.2
24°	1319.9
25°	998.8
26°	739.6
27°	541.6
28°	407.0
29°	316.4
30°	255.3
31°	211.2
32°	176.4
32.5°	160.9
33°	145.5
34°	118.4
35°	94.4
36°	74.3
37°	58.8
37.5°	52.6
38°	46.4
39°	38.7
40°	31.7
42.5°	20.9
45°	13.9



TEST NUMBER: P1250032
CATALOG NUMBER: P3AS20R409027D010 E3D1WH

CANDELA DISTRIBUTION (continued):

	0°
47.5°	8.5
50°	3.9
52.5°	1.5
55°	1.5
57.5°	0.8
60°	0.8
62.5°	0.8
65°	0.8
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)