

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1250040

Luminaire Tested: P3AS20R409027D010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1250040
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-22)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R409027D010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R40 optic, 2700K CCT AND, 90CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 690.9 lumens
Efficiency: N/A
Efficacy: 24.0 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1250040

CATALOG NUMBER: P3AS20R409027D010 E3DLD1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1250040

CATALOG NUMBER: P3AS20R409027D010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	104	102	103	101	99		99	98	96		96
2	106	100	96	92	104	98	94	91	95	92	89		92	89	87		89
3	100	92	87	82	98	91	86	81	88	84	80		86	82	79		83
4	94	85	79	74	92	84	78	74	82	77	73		80	75	72		78
5	89	79	73	68	87	78	72	67	76	71	67		75	70	66		73
6	84	74	67	62	82	73	67	62	71	66	61		70	65	61		68
7	79	69	62	57	78	68	62	57	67	61	57		65	60	57		64
8	75	64	58	53	74	64	58	53	63	57	53		62	56	53		61
9	71	60	54	50	70	60	54	50	59	53	49		58	53	49		57
10	67	57	51	46	66	56	50	46	56	50	46		55	50	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	155119
5°	152300
10°	143573
15°	130398
20°	114553
25°	97820
30°	81050
35°	62506
40°	44483
45°	29957
50°	16341
55°	11546
60°	10832
65°	10014
70°	8912
75°	8557
80°	6819
85°	5787

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 29957 cd/sqm

TEST NUMBER: P1250040

CATALOG NUMBER: P3AS20R409027D010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	64.5	9.3
10°-20°	160.0	23.2
20°-30°	185.0	26.8
30°-40°	145.8	21.1
40°-50°	74.8	10.8
50°-60°	28.6	4.1
60°-70°	18.9	2.7
70°-80°	10.3	1.5
80°-90°	3.0	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	409.5	59.3
0°-40°	555.3	80.4
0°-60°	658.7	95.3
0°-90°	690.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	690.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	707	
5°	692	65
15°	574	160
25°	404	185
35°	234	146
45°	97	75
55°	30	29
65°	19	19
75°	10	10
85°	2	3
90°	0	

TEST NUMBER: P1250040

CATALOG NUMBER: P3AS20R409027D010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	707.4
2.5°	703.5
5°	691.9
7.5°	671.8
10°	644.8
12.5°	613.1
15°	574.4
17.5°	534.2
20°	490.9
22.5°	446.8
25°	404.3
27.5°	361.8
30°	320.1
32.5°	277.5
35°	233.5
37.5°	192.5
40°	155.4
42.5°	123.7
45°	96.6
47.5°	70.4
50°	47.9
52.5°	34.8
55°	30.2
57.5°	27.1
60°	24.7
62.5°	21.6
65°	19.3
67.5°	16.2
70°	13.9
72.5°	11.6
75°	10.1
77.5°	7.7
80°	5.4
82.5°	4.6
85°	2.3
87.5°	1.5
90°	0.0

(END OF REPORT)