

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1248700

Luminaire Tested: P3AS05R709027DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1248700
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-47)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R709027DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R70 optic, 2700K CCT AND, 90CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 231.0 lumens
Efficiency: N/A
Efficacy: 32.1 lumens/watt
Spacing Criteria (0/90/45): 0.97 / 0.97 / 0.98
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1248700
CATALOG NUMBER: P3AS05R709027DE010 E3DL1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1248700

CATALOG NUMBER: P3AS05R709027DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	104	110	107	105	103	103	101	100	100	98	97	96	95	94	92	92	92	92
2	106	101	96	93	104	99	95	92	96	92	90	93	90	88	90	88	86	84	84	84	84
3	100	93	88	83	98	92	87	82	89	85	81	86	83	80	84	81	79	77	77	77	77
4	94	86	80	75	93	85	79	75	83	78	74	81	76	73	79	75	72	70	70	70	70
5	89	80	73	69	87	79	73	68	77	72	68	75	71	67	74	70	66	65	65	65	65
6	84	74	68	63	82	73	67	63	72	66	62	70	65	62	69	65	61	60	60	60	60
7	79	69	62	58	78	68	62	58	67	61	57	66	61	57	65	60	57	55	55	55	55
8	75	65	58	53	74	64	58	53	63	57	53	62	57	53	61	56	53	51	51	51	51
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48	48	48	48
10	67	57	50	46	66	56	50	46	55	50	46	55	49	46	54	49	46	44	44	44	44

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	44711
5°	44178
10°	42907
15°	41090
20°	38480
25°	34962
30°	30207
35°	24066
40°	17547
45°	11536
50°	5390
55°	1682
60°	1623
65°	1557
70°	1475
75°	1525
80°	1389
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 11536 cd/sqm



TEST NUMBER: P1248700
 CATALOG NUMBER: P3AS05R709027DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	18.9	8.2
10°-20°	50.7	21.9
20°-30°	65.8	28.5
30°-40°	55.9	24.2
40°-50°	28.8	12.5
50°-60°	5.6	2.4
60°-70°	3.0	1.3
70°-80°	1.8	0.8
80°-90°	0.5	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	135.4	58.6
0°-40°	191.2	82.8
0°-60°	225.6	97.7
0°-90°	231.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	231.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	204	
5°	201	19
15°	181	51
25°	144	66
35°	90	56
45°	37	29
55°	4	6
65°	3	3
75°	2	2
85°	0	1
90°	0	



TEST NUMBER: P1248700
CATALOG NUMBER: P3AS05R709027DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	203.9
2.5°	203.2
5°	200.7
7.5°	197.1
10°	192.7
12.5°	187.2
15°	181.0
17.5°	173.4
20°	164.9
22.5°	155.3
25°	144.5
27.5°	132.4
30°	119.3
32.5°	104.8
35°	89.9
37.5°	75.2
40°	61.3
42.5°	48.2
45°	37.2
47.5°	27.3
50°	15.8
52.5°	6.9
55°	4.4
57.5°	4.1
60°	3.7
62.5°	3.4
65°	3.0
67.5°	2.8
70°	2.3
72.5°	2.1
75°	1.8
77.5°	1.4
80°	1.1
82.5°	0.7
85°	0.5
87.5°	0.2
90°	0.0

(END OF REPORT)