

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1250045

Luminaire Tested: P3AS20R409027D010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1250045
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-22)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R409027D010 E3DLD1WMH
Description: 3in Adjustable LED luminaire with, R40 optic, 2700K CCT AND, 90CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1410.0 lumens
Efficiency: N/A
Efficacy: 49.0 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1250045

CATALOG NUMBER: P3AS20R409027D010 E3DLD1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1250045

CATALOG NUMBER: P3AS20R409027D010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	104	102	103	101	99		99	98	96		96
2	106	100	96	92	104	98	94	91	95	92	89		92	89	87		89
3	100	92	87	82	98	91	86	81	88	84	80		86	82	79		83
4	94	85	79	74	92	84	78	74	82	77	73		80	75	72		78
5	89	79	73	68	87	78	72	67	76	71	67		75	70	66		73
6	84	74	67	62	82	73	67	62	71	66	61		70	65	61		68
7	79	69	62	57	78	68	62	57	67	61	57		65	60	57		64
8	75	64	58	53	74	64	57	53	63	57	53		62	56	53		61
9	71	60	54	50	70	60	54	50	59	53	49		58	53	49		57
10	67	57	51	46	66	56	50	46	56	50	46		55	50	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	316510
5°	310785
10°	292936
15°	266086
20°	233750
25°	199608
30°	165367
35°	127529
40°	90770
45°	61154
50°	33364
55°	23512
60°	22147
65°	20443
70°	18208
75°	17368
80°	13891
85°	11825

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 61154 cd/sqm

TEST NUMBER: P1250045

CATALOG NUMBER: P3AS20R409027D010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	131.7	9.3
10°-20°	326.5	23.2
20°-30°	377.4	26.8
30°-40°	297.5	21.1
40°-50°	152.7	10.8
50°-60°	58.4	4.1
60°-70°	38.6	2.7
70°-80°	21.0	1.5
80°-90°	6.2	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	835.6	59.3
0°-40°	1133.1	80.4
0°-60°	1344.2	95.3
0°-90°	1410.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1410.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1443	
5°	1412	132
15°	1172	327
25°	825	377
35°	476	297
45°	197	153
55°	62	58
65°	39	39
75°	20	21
85°	5	6
90°	0	

TEST NUMBER: P1250045

CATALOG NUMBER: P3AS20R409027D010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1443.4
2.5°	1435.5
5°	1411.9
7.5°	1370.9
10°	1315.6
12.5°	1251.0
15°	1172.1
17.5°	1090.1
20°	1001.7
22.5°	911.8
25°	825.0
27.5°	738.3
30°	653.1
32.5°	566.3
35°	476.4
37.5°	392.8
40°	317.1
42.5°	252.4
45°	197.2
47.5°	143.6
50°	97.8
52.5°	71.0
55°	61.5
57.5°	55.2
60°	50.5
62.5°	44.2
65°	39.4
67.5°	33.1
70°	28.4
72.5°	23.7
75°	20.5
77.5°	15.8
80°	11.0
82.5°	9.5
85°	4.7
87.5°	3.2
90°	0.0

(END OF REPORT)