

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1248762

Luminaire Tested: P3AS09R159027DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1248762
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-2)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R159027DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R15 optic, 2700K CCT AND, 90CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 264.0 lumens
Efficiency: N/A
Efficacy: 23.8 lumens/watt
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1248762

CATALOG NUMBER: P3AS09R159027DE010 E3DLD1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1248762

CATALOG NUMBER: P3AS09R159027DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	109	107	104	110	107	105	102	103	101	99		99	98	96		96
2	106	100	96	92	104	99	95	91	95	92	89		92	90	87		90
3	100	93	87	83	98	91	86	82	89	84	81		86	82	79		84
4	94	86	80	75	92	85	79	74	82	77	73		80	76	73		78
5	89	80	73	68	87	79	73	68	77	72	67		75	71	67		74
6	84	74	68	63	83	73	67	63	72	66	62		70	66	62		69
7	80	69	63	58	78	69	63	58	67	62	58		66	61	58		65
8	76	65	59	54	74	65	58	54	63	58	54		62	57	54		61
9	72	61	55	51	71	61	55	51	60	54	50		59	54	50		58
10	68	58	52	48	67	57	51	47	57	51	47		56	51	47		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	66596
5°	64781
10°	59206
15°	51850
20°	44477
25°	37139
30°	29726
35°	22299
40°	16173
45°	10575
50°	6618
55°	4473
60°	3947
65°	3632
70°	3462
75°	3135
80°	2904
85°	2516

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10575 cd/sqm

TEST NUMBER: P1248762

CATALOG NUMBER: P3AS09R159027DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	27.2	10.3
10°-20°	63.6	24.1
20°-30°	70.1	26.6
30°-40°	52.5	19.9
40°-50°	27.2	10.3
50°-60°	11.3	4.3
60°-70°	7.0	2.6
70°-80°	3.9	1.5
80°-90°	1.1	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	160.9	61.0
0°-40°	213.5	80.9
0°-60°	252.0	95.4
0°-90°	264.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	264.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	304	
5°	294	27
15°	228	64
25°	154	70
35°	83	53
45°	34	27
55°	12	11
65°	7	7
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1248762

CATALOG NUMBER: P3AS09R159027DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	303.7
1°	304.0
2°	303.0
3°	301.0
4°	298.0
5°	294.3
6°	289.6
7°	284.6
8°	278.6
9°	272.2
10°	265.9
12.5°	247.5
15°	228.4
17.5°	209.4
20°	190.6
22.5°	171.6
25°	153.5
27.5°	135.5
30°	117.4
32.5°	99.7
35°	83.3
37.5°	69.2
40°	56.5
42.5°	44.8
45°	34.1
47.5°	25.8
50°	19.4
52.5°	14.4
55°	11.7
57.5°	10.4
60°	9.0
62.5°	8.0
65°	7.0
67.5°	6.0
70°	5.4
72.5°	4.3
75°	3.7
77.5°	3.0
80°	2.3
82.5°	1.7
85°	1.0
87.5°	0.3
90°	0.0

(END OF REPORT)