

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1248767

Luminaire Tested: P3AS09R159027DE010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1248767
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-2)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R159027DE010 E3DLD1WMH
Description: 3in Adjustable LED luminaire with, R15 optic, 2700K CCT AND, 90CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 539.0 lumens
Efficiency: N/A
Efficacy: 48.6 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1248767

CATALOG NUMBER: P3AS09R159027DE010 E3DLD1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1248767

CATALOG NUMBER: P3AS09R159027DE010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	109	107	104	110	107	105	102	103	101	99		99	98	96		96
2	106	100	96	92	104	99	95	91	95	92	89		92	90	87		90
3	100	93	87	83	98	91	86	82	89	84	81		86	82	79		84
4	94	86	80	75	92	85	79	74	82	77	73		80	76	73		78
5	89	80	73	68	87	79	73	68	77	72	67		75	71	67		74
6	84	74	68	63	83	73	67	63	72	66	62		70	66	62		69
7	80	69	63	58	78	69	63	58	67	62	58		66	61	57		65
8	76	65	59	54	74	65	58	54	63	58	54		62	57	54		61
9	72	61	55	51	71	61	55	51	60	54	50		59	54	50		58
10	68	58	52	48	67	57	51	47	57	51	47		56	51	47		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	135954
5°	132269
10°	120862
15°	105880
20°	90821
25°	75827
30°	60693
35°	45508
40°	33033
45°	21584
50°	13509
55°	9137
60°	8070
65°	7420
70°	6988
75°	6354
80°	6061
85°	5032

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 21584 cd/sqm

TEST NUMBER: P1248767

CATALOG NUMBER: P3AS09R159027DE010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	55.4	10.3
10°-20°	130.0	24.1
20°-30°	143.2	26.6
30°-40°	107.2	19.9
40°-50°	55.6	10.3
50°-60°	23.0	4.3
60°-70°	14.3	2.6
70°-80°	8.0	1.5
80°-90°	2.3	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	328.6	61.0
0°-40°	435.8	80.9
0°-60°	514.4	95.4
0°-90°	539.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	539.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	620	
5°	601	55
15°	466	130
25°	313	143
35°	170	107
45°	70	56
55°	24	23
65°	14	14
75°	8	8
85°	2	2
90°	0	

TEST NUMBER: P1248767

CATALOG NUMBER: P3AS09R159027DE010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	620.0
1°	620.7
2°	618.6
3°	614.5
4°	608.4
5°	600.9
6°	591.3
7°	581.1
8°	568.8
9°	555.8
10°	542.8
12.5°	505.3
15°	466.4
17.5°	427.5
20°	389.2
22.5°	350.3
25°	313.4
27.5°	276.5
30°	239.7
32.5°	203.5
35°	170.0
37.5°	141.3
40°	115.4
42.5°	91.5
45°	69.6
47.5°	52.6
50°	39.6
52.5°	29.4
55°	23.9
57.5°	21.2
60°	18.4
62.5°	16.4
65°	14.3
67.5°	12.3
70°	10.9
72.5°	8.9
75°	7.5
77.5°	6.1
80°	4.8
82.5°	3.4
85°	2.0
87.5°	0.7
90°	0.0

(END OF REPORT)