

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1250099

Luminaire Tested: P3AS20R509027D010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1250099
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-30)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R509027D010 E3DLD1WMH
Description: 3in Adjustable LED luminaire with, R50 optic, 2700K CCT AND, 90CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1382.0 lumens
Efficiency: N/A
Efficacy: 48.0 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.93
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1250099

CATALOG NUMBER: P3AS20R509027D010 E3DLD1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1250099

CATALOG NUMBER: P3AS20R509027D010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	102	103	101	99		99	97	96		95
2	106	100	95	91	103	98	94	90	95	91	88		92	89	86		89
3	99	92	86	81	97	90	85	81	88	83	79		85	81	78		83
4	93	85	78	73	91	83	77	73	81	76	72		79	75	71		77
5	88	78	72	67	86	77	71	66	75	70	66		74	69	65		72
6	83	73	66	61	81	72	65	61	70	65	60		69	64	60		67
7	78	68	61	56	77	67	61	56	66	60	56		64	59	55		63
8	74	63	57	52	73	63	56	52	61	56	52		60	55	51		59
9	70	59	53	48	69	59	52	48	58	52	48		57	52	48		56
10	66	56	49	45	65	55	49	45	54	49	45		54	48	45		53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	280855
5°	276711
10°	264457
15°	244928
20°	220099
25°	193487
30°	164532
35°	133418
40°	100245
45°	64565
50°	30669
55°	24123
60°	22849
65°	21273
70°	19234
75°	17368
80°	15911
85°	15851

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 64565 cd/sqm

TEST NUMBER: P1250099

CATALOG NUMBER: P3AS20R509027D010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	117.8	8.5
10°-20°	300.8	21.8
20°-30°	365.5	26.4
30°-40°	309.9	22.4
40°-50°	161.0	11.6
50°-60°	58.1	4.2
60°-70°	40.2	2.9
70°-80°	21.8	1.6
80°-90°	6.9	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	784.1	56.7
0°-40°	1094.0	79.2
0°-60°	1313.1	95.0
0°-90°	1382.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1382.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1281	
5°	1257	118
15°	1079	301
25°	800	365
35°	498	310
45°	208	161
55°	63	58
65°	41	40
75°	20	22
85°	6	7
90°	0	

TEST NUMBER: P1250099

CATALOG NUMBER: P3AS20R509027D010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1280.8
2.5°	1276.0
5°	1257.1
7.5°	1228.7
10°	1187.7
12.5°	1135.7
15°	1078.9
17.5°	1014.2
20°	943.2
22.5°	870.7
25°	799.7
27.5°	725.6
30°	649.8
32.5°	574.1
35°	498.4
37.5°	424.3
40°	350.2
42.5°	279.2
45°	208.2
47.5°	138.8
50°	89.9
52.5°	69.4
55°	63.1
57.5°	56.8
60°	52.1
62.5°	45.7
65°	41.0
67.5°	34.7
70°	30.0
72.5°	25.2
75°	20.5
77.5°	15.8
80°	12.6
82.5°	9.5
85°	6.3
87.5°	3.2
90°	0.0

(END OF REPORT)