

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1248859

Luminaire Tested: P3AS09R309027DE010 E3DLP1H

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1248859
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-13)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R309027DE010 E3DLP1H
Description: 3in Adjustable LED luminaire with, R30 optic, 2700K CCT AND, 90CRI , E3DLP1H TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 441.0 lumens
Efficiency: N/A
Efficacy: 39.7 lumens/watt
Spacing Criteria (0/90/45): 0.66 / 0.66 / 0.7
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1248859
CATALOG NUMBER: P3AS09R309027DE010 E3DLP1H

Luminous Intensity Polar Plot





TEST NUMBER: P1248859
 CATALOG NUMBER: P3AS09R309027DE010 E3DLP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93	93	93	93
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86	86	86	86
3	102	95	90	86	100	94	89	85	91	87	84	89	86	83	87	84	82	80	80	80	80
4	97	89	84	79	95	88	83	79	86	81	78	84	80	77	82	79	76	74	74	74	74
5	92	84	78	73	90	83	77	73	81	76	72	79	75	72	78	74	71	70	70	70	70
6	88	79	73	68	86	78	72	68	76	71	68	75	71	67	74	70	67	65	65	65	65
7	83	74	68	64	82	74	68	64	72	67	63	71	67	63	70	66	63	61	61	61	61
8	80	70	64	60	78	70	64	60	69	63	60	67	63	60	67	62	59	58	58	58	58
9	76	67	61	57	75	66	60	57	65	60	56	64	60	56	63	59	56	55	55	55	55
10	73	63	58	54	72	63	57	54	62	57	53	61	57	53	60	56	53	52	52	52	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	150690
5°	146004
10°	131550
15°	108831
20°	84264
25°	63197
30°	45880
35°	30570
40°	18778
45°	11040
50°	6755
55°	5505
60°	4780
65°	3891
70°	3526
75°	3474
80°	2652
85°	3522

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 11040 cd/sqm



TEST NUMBER: P1248859
 CATALOG NUMBER: P3AS09R309027DE010 E3DLP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	61.0	13.8
10°-20°	132.0	29.9
20°-30°	120.1	27.2
30°-40°	72.6	16.5
40°-50°	29.1	6.6
50°-60°	12.9	2.9
60°-70°	7.8	1.8
70°-80°	4.2	1.0
80°-90°	1.2	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	313.1	71.0
0°-40°	385.7	87.5
0°-60°	427.8	97.0
0°-90°	441.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	441.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	687	
5°	663	61
15°	479	132
25°	261	120
35°	114	73
45°	36	29
55°	14	13
65°	8	8
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P1248859
CATALOG NUMBER: P3AS09R309027DE010 E3DLP1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	687.2
1°	686.6
2°	683.8
3°	679.0
4°	672.2
5°	663.3
6°	652.4
7°	640.7
8°	625.7
9°	608.6
10°	590.8
11°	570.3
12°	548.4
13°	526.5
14°	502.6
15°	479.4
17.5°	418.5
20°	361.1
22.5°	307.7
25°	261.2
27.5°	218.8
30°	181.2
32.5°	146.3
35°	114.2
37.5°	87.5
40°	65.6
42.5°	47.9
45°	35.6
47.5°	26.7
50°	19.8
52.5°	15.7
55°	14.4
57.5°	12.3
60°	10.9
62.5°	8.9
65°	7.5
67.5°	6.8
70°	5.5
72.5°	4.8
75°	4.1
77.5°	3.4
80°	2.1
82.5°	1.4
85°	1.4
87.5°	0.7



TEST NUMBER: P1248859
CATALOG NUMBER: P3AS09R309027DE010 E3DLP1H

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)