

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1248959

Luminaire Tested: P3AS09R509027DE010 E3D1WMH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1248959
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-13)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R509027DE010 E3D1WMH
Description: 3in Adjustable LED luminaire with, R50 optic, 2700K CCT AND, 90CRI , E3D1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 949.0 lumens
Efficiency: N/A
Efficacy: 85.5 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.77
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1248959

CATALOG NUMBER: P3AS09R509027DE010 E3D1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1248959

CATALOG NUMBER: P3AS09R509027DE010 E3D1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	109	107	112	110	108	106	105	104	102		102	101	99		98
2	109	105	101	98	107	103	100	97	100	97	95		97	95	93		94
3	105	99	95	91	103	98	94	90	95	92	89		93	90	88		91
4	100	94	89	85	99	92	88	85	90	87	84		88	85	83		87
5	96	89	84	80	94	88	83	79	86	82	79		84	81	78		83
6	92	84	79	75	91	83	78	75	82	78	74		81	77	74		79
7	88	80	75	71	87	79	74	71	78	74	70		77	73	70		76
8	84	76	71	67	83	76	71	67	75	70	67		74	69	66		73
9	81	73	67	64	80	72	67	64	71	67	63		70	66	63		70
10	78	69	64	61	77	69	64	61	68	64	60		67	63	60		67

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	331640
5°	322803
10°	308055
15°	278889
20°	241264
25°	197915
30°	113688
35°	35309
40°	9475
45°	3318
50°	785
55°	268
60°	132
65°	156
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3318 cd/sqm

TEST NUMBER: P1248959

CATALOG NUMBER: P3AS09R509027DE010 E3D1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	137.4	14.5
10°-20°	340.4	35.9
20°-30°	357.8	37.7
30°-40°	102.4	10.8
40°-50°	10.0	1.1
50°-60°	0.8	0.1
60°-70°	0.3	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	835.5	88.0
0°-40°	937.9	98.8
0°-60°	948.7	100.0
0°-90°	949.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	949.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1512	
5°	1466	137
15°	1228	340
25°	818	358
35°	132	102
45°	11	10
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1248959

CATALOG NUMBER: P3AS09R509027DE010 E3D1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1512.4
1°	1510.0
2°	1503.3
3°	1493.6
4°	1480.6
5°	1466.5
6°	1451.5
7°	1435.4
8°	1420.3
9°	1402.9
10°	1383.5
11°	1361.0
12°	1335.3
13°	1303.1
14°	1268.3
15°	1228.5
16°	1186.3
17°	1145.4
18°	1103.6
19°	1066.7
20°	1033.9
21°	1002.5
22°	966.6
23°	925.4
24°	877.2
25°	818.0
26°	753.7
27°	682.0
28°	610.7
29°	533.7
30°	449.0
31°	369.6
32°	296.7
32.5°	264.8
33°	232.7
34°	178.5
35°	131.9
36°	96.8
37°	72.0
37.5°	62.3
38°	53.9
39°	41.9
40°	33.1
42.5°	18.8
45°	10.7

TEST NUMBER: P1248959

CATALOG NUMBER: P3AS09R509027DE010 E3D1WMH

CANDELA DISTRIBUTION (continued):

	0°
47.5°	6.0
50°	2.3
52.5°	1.0
55°	0.7
57.5°	0.7
60°	0.3
62.5°	0.3
65°	0.3
67.5°	0.3
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)