

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1250192

Luminaire Tested: P3AS20R659027D010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1250192
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-41)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R659027D010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R65 optic, 2700K CCT AND, 90CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1094.0 lumens
Efficiency: N/A
Efficacy: 38.0 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1250192

CATALOG NUMBER: P3AS20R659027D010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1250192

CATALOG NUMBER: P3AS20R659027D010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		96
2	107	101	97	93	104	100	96	92	96	93	90		93	91	88		90
3	101	94	88	84	99	92	87	83	90	85	82		87	84	81		85
4	95	87	81	76	93	86	80	76	84	79	75		82	78	74		80
5	90	81	75	70	88	80	74	70	78	73	69		77	72	69		75
6	85	76	69	65	84	75	69	65	73	68	64		72	67	64		71
7	81	71	65	60	79	70	64	60	69	64	60		68	63	59		67
8	77	67	60	56	75	66	60	56	65	59	56		64	59	55		63
9	73	63	57	52	72	62	56	52	61	56	52		60	55	52		59
10	69	59	53	49	68	59	53	49	58	53	49		57	52	49		56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	278070
5°	271164
10°	252523
15°	226290
20°	195434
25°	162566
30°	128197
35°	95004
40°	65466
45°	40593
50°	22072
55°	13878
60°	11753
65°	10637
70°	9104
75°	8049
80°	7956
85°	8051

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 40593 cd/sqm

TEST NUMBER: P1250192

CATALOG NUMBER: P3AS20R659027D010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	114.5	10.5
10°-20°	277.0	25.3
20°-30°	306.3	28.0
30°-40°	222.5	20.3
40°-50°	104.2	9.5
50°-60°	35.1	3.2
60°-70°	20.3	1.9
70°-80°	10.6	1.0
80°-90°	3.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	697.8	63.8
0°-40°	920.3	84.1
0°-60°	1059.7	96.9
0°-90°	1094.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1094.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1268	
5°	1232	114
15°	997	277
25°	672	306
35°	355	223
45°	131	104
55°	36	35
65°	20	20
75°	10	11
85°	3	3
90°	0	

TEST NUMBER: P1250192

CATALOG NUMBER: P3AS20R659027D010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1268.1
2.5°	1260.2
5°	1231.9
7.5°	1189.3
10°	1134.1
12.5°	1069.4
15°	996.8
17.5°	918.0
20°	837.5
22.5°	753.9
25°	671.9
27.5°	588.3
30°	506.3
32.5°	427.4
35°	354.9
37.5°	288.6
40°	228.7
42.5°	175.1
45°	130.9
47.5°	94.6
50°	64.7
52.5°	44.2
55°	36.3
57.5°	31.5
60°	26.8
62.5°	23.7
65°	20.5
67.5°	17.4
70°	14.2
72.5°	12.6
75°	9.5
77.5°	7.9
80°	6.3
82.5°	4.7
85°	3.2
87.5°	1.6
90°	0.0

(END OF REPORT)