

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1250202

Luminaire Tested: P3AS20R709027D010 E3D1WH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1250202
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-17)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R709027D010 E3D1WH
Description: 3in Adjustable LED luminaire with, R70 optic, 2700K CCT AND, 90CRI , E3D1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1882.0 lumens
Efficiency: N/A
Efficacy: 65.3 lumens/watt
Spacing Criteria (0/90/45): 1.02 / 1.02 / 1.06
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1250202

CATALOG NUMBER: P3AS20R709027D010 E3D1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1250202

CATALOG NUMBER: P3AS20R709027D010 E3D1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	94	89	85	99	93	88	84	90	86	83		88	84	81		86
4	95	87	81	77	94	86	81	77	84	79	76		82	78	75		80
5	90	81	75	70	88	80	74	70	78	73	69		77	72	69		75
6	85	75	69	64	83	75	69	64	73	68	64		72	67	63		70
7	80	70	64	59	79	70	63	59	68	63	59		67	62	58		66
8	76	66	59	55	75	65	59	55	64	58	54		63	58	54		62
9	72	61	55	51	71	61	55	51	60	54	50		59	54	50		58
10	68	58	51	47	67	57	51	47	56	51	47		55	50	47		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	365936
5°	345057
10°	327182
15°	321296
20°	309707
25°	291936
30°	289867
35°	252434
40°	163277
45°	77186
50°	10814
55°	879
60°	658
65°	778
70°	513
75°	678
80°	1010
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 77186 cd/sqm

TEST NUMBER: P1250202

CATALOG NUMBER: P3AS20R709027D010 E3D1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	146.4	7.8
10°-20°	397.5	21.1
20°-30°	562.3	29.9
30°-40°	565.1	30.0
40°-50°	203.2	10.8
50°-60°	5.5	0.3
60°-70°	1.2	0.1
70°-80°	0.8	0.0
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1106.1	58.8
0°-40°	1671.2	88.8
0°-60°	1879.8	99.9
0°-90°	1882.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1882.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1669	
5°	1568	146
15°	1415	397
25°	1207	562
35°	943	565
45°	249	203
55°	2	5
65°	2	1
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1250202

CATALOG NUMBER: P3AS20R709027D010 E3D1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1668.8
1°	1664.2
2°	1649.5
3°	1626.3
4°	1596.9
5°	1567.6
6°	1539.7
7°	1518.1
8°	1498.8
9°	1483.3
10°	1469.4
11°	1457.8
12°	1447.0
13°	1436.2
14°	1426.1
15°	1415.3
16°	1402.2
17°	1388.2
18°	1371.2
19°	1350.4
20°	1327.2
21°	1301.7
22°	1276.2
23°	1251.4
24°	1227.5
25°	1206.6
26°	1191.9
27°	1180.3
28°	1171.0
29°	1160.2
30°	1144.8
31°	1122.3
32°	1090.7
32.5°	1072.9
33°	1048.9
34°	1001.8
35°	943.0
36°	878.1
37°	804.7
37.5°	770.6
38°	724.3
39°	641.6
40°	570.4
42.5°	395.0
45°	248.9

TEST NUMBER: P1250202

CATALOG NUMBER: P3AS20R709027D010 E3D1WH

CANDELA DISTRIBUTION (continued):

	0°
47.5°	133.7
50°	31.7
52.5°	3.9
55°	2.3
57.5°	2.3
60°	1.5
62.5°	1.5
65°	1.5
67.5°	0.8
70°	0.8
72.5°	0.8
75°	0.8
77.5°	0.8
80°	0.8
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)