

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1250210

Luminaire Tested: P3AS20R709027D010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1250210
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-45)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R709027D010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R70 optic, 2700K CCT AND, 90CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 556.0 lumens
Efficiency: N/A
Efficacy: 19.3 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1250210

CATALOG NUMBER: P3AS20R709027D010 E3DLP1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1250210

CATALOG NUMBER: P3AS20R709027D010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	104	110	107	105	103	103	101	100		100	98	97		96
2	106	101	97	93	104	99	95	92	96	93	90		93	90	88		90
3	100	93	88	83	98	92	87	83	89	85	81		87	83	80		84
4	95	86	80	76	93	85	80	75	83	78	74		81	77	73		79
5	89	80	74	69	88	79	73	69	78	72	68		76	71	68		74
6	85	75	68	64	83	74	68	64	73	67	63		71	66	63		70
7	80	70	64	59	79	69	63	59	68	62	58		67	62	58		66
8	76	66	59	55	75	65	59	55	64	58	54		63	58	54		62
9	72	62	55	51	71	61	55	51	60	55	51		59	54	51		58
10	69	58	52	48	67	58	52	48	57	51	48		56	51	48		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	130406
5°	128021
10°	120728
15°	109558
20°	95838
25°	80835
30°	66187
35°	51343
40°	36755
45°	23258
50°	11599
55°	7111
60°	6096
65°	5604
70°	4937
75°	4575
80°	3915
85°	3774

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 23258 cd/sqm

TEST NUMBER: P1250210

CATALOG NUMBER: P3AS20R709027D010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.3	9.8
10°-20°	134.3	24.2
20°-30°	152.9	27.5
30°-40°	119.6	21.5
40°-50°	58.7	10.6
50°-60°	18.1	3.2
60°-70°	10.7	1.9
70°-80°	5.7	1.0
80°-90°	1.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	341.5	61.4
0°-40°	461.1	82.9
0°-60°	537.9	96.7
0°-90°	556.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	556.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	595	
5°	582	54
15°	483	134
25°	334	153
35°	192	120
45°	75	59
55°	19	18
65°	11	11
75°	5	6
85°	2	2
90°	0	

TEST NUMBER: P1250210

CATALOG NUMBER: P3AS20R709027D010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	594.7
2.5°	591.7
5°	581.6
7.5°	565.4
10°	542.2
12.5°	515.1
15°	482.6
17.5°	447.8
20°	410.7
22.5°	372.0
25°	334.1
27.5°	297.0
30°	261.4
32.5°	225.8
35°	191.8
37.5°	159.3
40°	128.4
42.5°	99.8
45°	75.0
47.5°	52.6
50°	34.0
52.5°	22.4
55°	18.6
57.5°	16.2
60°	13.9
62.5°	12.4
65°	10.8
67.5°	9.3
70°	7.7
72.5°	6.2
75°	5.4
77.5°	4.6
80°	3.1
82.5°	2.3
85°	1.5
87.5°	0.8
90°	0.0

(END OF REPORT)