

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1249005

Luminaire Tested: P3AS09R559027DE010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1249005
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-35)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R559027DE010 E3DLP1WH
Description: 3in Adjustable LED luminaire with, R55 optic, 2700K CCT AND, 90CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 745.0 lumens
Efficiency: N/A
Efficacy: 67.1 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.81
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1249005
CATALOG NUMBER: P3AS09R559027DE010 E3DLP1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1249005
 CATALOG NUMBER: P3AS09R559027DE010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93			
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87			
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	85	82	81			
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	82	79	77	75			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70			
6	88	79	73	69	86	78	73	68	77	72	68	75	71	68	74	70	67	66			
7	84	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	62			
8	80	70	64	60	78	70	64	60	69	63	60	67	63	60	67	62	59	58			
9	76	66	61	57	75	66	60	56	65	60	56	64	59	56	63	59	56	55			
10	73	63	57	53	72	62	57	53	62	57	53	61	56	53	60	56	53	52			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	204567
5°	202487
10°	195543
15°	180750
20°	155974
25°	123201
30°	87381
35°	56349
40°	33835
45°	19072
50°	10268
55°	3670
60°	3289
65°	3217
70°	3077
75°	2881
80°	2652
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 19072 cd/sqm



TEST NUMBER: P1249005
 CATALOG NUMBER: P3AS09R559027DE010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	86.5	11.6
10°-20°	220.2	29.6
20°-30°	230.7	31.0
30°-40°	134.6	18.1
40°-50°	50.4	6.8
50°-60°	11.9	1.6
60°-70°	6.1	0.8
70°-80°	3.6	0.5
80°-90°	1.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	537.4	72.1
0°-40°	672.0	90.2
0°-60°	734.3	98.6
0°-90°	745.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	745.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	933	
5°	920	87
15°	796	220
25°	509	231
35°	210	135
45°	62	50
55°	10	12
65°	6	6
75°	3	4
85°	1	1
90°	0	



TEST NUMBER: P1249005
CATALOG NUMBER: P3AS09R559027DE010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	932.9
2.5°	930.2
5°	919.9
7.5°	903.5
10°	878.2
12.5°	842.7
15°	796.2
17.5°	737.5
20°	668.4
22.5°	591.2
25°	509.2
27.5°	425.1
30°	345.1
32.5°	272.7
35°	210.5
37.5°	159.9
40°	118.2
42.5°	84.7
45°	61.5
47.5°	44.4
50°	30.1
52.5°	17.1
55°	9.6
57.5°	8.2
60°	7.5
62.5°	6.8
65°	6.2
67.5°	5.5
70°	4.8
72.5°	4.1
75°	3.4
77.5°	2.7
80°	2.1
82.5°	1.4
85°	0.7
87.5°	0.7
90°	0.0

(END OF REPORT)