

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1250215

Luminaire Tested: P3AS20R709027D010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1250215
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-45)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R709027D010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R70 optic, 2700K CCT AND, 90CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1134.0 lumens
Efficiency: N/A
Efficacy: 39.4 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1250215

CATALOG NUMBER: P3AS20R709027D010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1250215

CATALOG NUMBER: P3AS20R709027D010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	104	110	107	105	103	103	101	100		100	98	97		96
2	106	101	97	93	104	99	95	92	96	93	90		93	90	88		90
3	100	93	88	83	98	92	87	83	89	85	81		87	83	80		84
4	95	86	80	76	93	85	80	75	83	78	74		81	77	73		79
5	89	80	74	69	88	79	73	69	78	72	68		76	71	68		74
6	85	75	68	64	83	74	68	64	73	67	63		71	66	63		70
7	80	70	64	59	79	69	63	59	68	62	58		67	62	58		66
8	76	66	59	55	75	65	59	55	64	58	54		63	58	54		62
9	72	62	55	51	71	61	55	51	60	55	51		59	54	51		58
10	69	58	52	48	67	58	52	48	57	51	48		56	51	48		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	265987
5°	261104
10°	246221
15°	223452
20°	195457
25°	164864
30°	135008
35°	104721
40°	74940
45°	47447
50°	23675
55°	14489
60°	12455
65°	11467
70°	10130
75°	9320
80°	7956
85°	8051

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 47447 cd/sqm

TEST NUMBER: P1250215

CATALOG NUMBER: P3AS20R709027D010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	110.7	9.8
10°-20°	273.9	24.2
20°-30°	311.9	27.5
30°-40°	243.9	21.5
40°-50°	119.8	10.6
50°-60°	36.8	3.2
60°-70°	21.8	1.9
70°-80°	11.6	1.0
80°-90°	3.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	696.5	61.4
0°-40°	940.4	82.9
0°-60°	1097.1	96.7
0°-90°	1134.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1134.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1213	
5°	1186	111
15°	984	274
25°	681	312
35°	391	244
45°	153	120
55°	38	37
65°	22	22
75°	11	12
85°	3	3
90°	0	

TEST NUMBER: P1250215

CATALOG NUMBER: P3AS20R709027D010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1213.0
2.5°	1206.7
5°	1186.2
7.5°	1153.1
10°	1105.8
12.5°	1050.5
15°	984.3
17.5°	913.3
20°	837.6
22.5°	758.7
25°	681.4
27.5°	605.7
30°	533.2
32.5°	460.6
35°	391.2
37.5°	324.9
40°	261.8
42.5°	203.5
45°	153.0
47.5°	107.3
50°	69.4
52.5°	45.7
55°	37.9
57.5°	33.1
60°	28.4
62.5°	25.2
65°	22.1
67.5°	18.9
70°	15.8
72.5°	12.6
75°	11.0
77.5°	9.5
80°	6.3
82.5°	4.7
85°	3.2
87.5°	1.6
90°	0.0

(END OF REPORT)