

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1249066

Luminaire Tested: P3AS09R709027DE010 E3CB1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1249066
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-48)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R709027DE010 E3CB1MMS
Description: 3in Adjustable LED luminaire with, R70 optic, 2700K CCT AND, 90CRI , E3CB1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 855.0 lumens
Efficiency: N/A
Efficacy: 77.0 lumens/watt
Spacing Criteria (0/90/45): 1.01 / 1.01 / 1.03
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1249066

CATALOG NUMBER: P3AS09R709027DE010 E3CB1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1249066

CATALOG NUMBER: P3AS09R709027DE010 E3CB1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	97	94	105	100	96	93	97	94	91		94	91	89		91
3	101	94	89	85	99	93	88	84	90	86	83		88	84	81		85
4	95	87	81	77	94	86	81	76	84	79	75		82	78	75		80
5	90	81	75	70	88	80	74	70	78	73	69		77	72	69		75
6	85	75	69	64	83	75	69	64	73	68	64		72	67	63		70
7	80	70	64	59	79	70	64	59	68	63	59		67	62	59		66
8	76	66	59	55	75	65	59	55	64	58	55		63	58	54		62
9	72	62	55	51	71	61	55	51	60	55	51		59	54	50		58
10	68	58	52	47	67	57	51	47	56	51	47		56	51	47		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	169789
5°	162007
10°	154150
15°	150012
20°	144469
25°	136726
30°	127184
35°	106836
40°	68843
45°	32003
50°	8392
55°	2103
60°	2105
65°	1764
70°	1731
75°	1779
80°	1768
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 32003 cd/sqm

TEST NUMBER: P1249066

CATALOG NUMBER: P3AS09R709027DE010 E3CB1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	68.9	8.1
10°-20°	185.7	21.7
20°-30°	259.4	30.3
30°-40°	240.5	28.1
40°-50°	86.2	10.1
50°-60°	7.3	0.9
60°-70°	3.6	0.4
70°-80°	2.4	0.3
80°-90°	1.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	514.0	60.1
0°-40°	754.5	88.2
0°-60°	848.1	99.2
0°-90°	855.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	855.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	774	
5°	736	69
15°	661	186
25°	565	259
35°	399	241
45°	103	86
55°	6	7
65°	3	4
75°	2	2
85°	1	1
90°	0	

TEST NUMBER: P1249066

CATALOG NUMBER: P3AS09R709027DE010 E3CB1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	774.3
2.5°	762.6
5°	736.0
7.5°	711.4
10°	692.3
12.5°	676.5
15°	660.8
17.5°	641.7
20°	619.1
22.5°	593.2
25°	565.1
27.5°	536.4
30°	502.3
32.5°	458.5
35°	399.1
37.5°	323.2
40°	240.5
42.5°	164.0
45°	103.2
47.5°	57.4
50°	24.6
52.5°	8.2
55°	5.5
57.5°	4.8
60°	4.8
62.5°	4.1
65°	3.4
67.5°	3.4
70°	2.7
72.5°	2.7
75°	2.1
77.5°	2.1
80°	1.4
82.5°	1.4
85°	0.7
87.5°	0.7
90°	0.0

(END OF REPORT)