

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1249074

Luminaire Tested: P3AS09R709027DE010 E3D1WH

Issue Date: 1/29/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1249074  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-17)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R709027DE010 E3D1WH  
Description: 3in Adjustable LED luminaire with, R70 optic, 2700K CCT AND, 90CRI , E3D1WH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 814.9 lumens  
Efficiency: N/A  
Efficacy: 73.4 lumens/watt  
Spacing Criteria (0/90/45): 1.02 / 1.02 / 1.06  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 11.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1249074  
CATALOG NUMBER: P3AS09R709027DE010 E3D1WH

### Luminous Intensity Polar Plot





TEST NUMBER: P1249074  
 CATALOG NUMBER: P3AS09R709027DE010 E3D1WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85			85
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	86	83	80	79			79
4	95	87	81	77	94	86	81	77	84	79	76	82	78	75	80	77	74	72			72
5	90	81	75	70	88	80	74	70	78	73	69	77	72	69	75	71	68	66			66
6	85	75	69	64	83	75	69	64	73	68	64	72	67	63	70	66	63	61			61
7	80	70	64	59	79	70	63	59	68	63	59	67	62	58	66	61	58	57			57
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52			52
9	72	61	55	51	71	61	55	51	60	54	50	59	54	50	58	53	50	49			49
10	68	58	51	47	67	57	51	47	56	51	47	55	50	47	55	50	47	45			45

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	158474
5°	149416
10°	141681
15°	139138
20°	134108
25°	126419
30°	125513
35°	109326
40°	70704
45°	33430
50°	4674
55°	382
60°	307
65°	363
70°	192
75°	254
80°	379
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 33430 cd/sqm



TEST NUMBER: P1249074  
 CATALOG NUMBER: P3AS09R709027DE010 E3D1WH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	63.4	7.8
10°-20°	172.1	21.1
20°-30°	243.5	29.9
30°-40°	244.7	30.0
40°-50°	88.0	10.8
50°-60°	2.4	0.3
60°-70°	0.5	0.1
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	479.0	58.8
0°-40°	723.7	88.8
0°-60°	814.0	99.9
0°-90°	814.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	814.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	723	
5°	679	63
15°	613	172
25°	522	243
35°	408	245
45°	108	88
55°	1	2
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1249074  
CATALOG NUMBER: P3AS09R709027DE010 E3D1WH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	722.7
1°	720.7
2°	714.3
3°	704.3
4°	691.6
5°	678.8
6°	666.8
7°	657.4
8°	649.0
9°	642.4
10°	636.3
11°	631.3
12°	626.6
13°	621.9
14°	617.6
15°	612.9
16°	607.2
17°	601.2
18°	593.8
19°	584.8
20°	574.7
21°	563.7
22°	552.6
23°	541.9
24°	531.6
25°	522.5
26°	516.2
27°	511.1
28°	507.1
29°	502.4
30°	495.7
31°	486.0
32°	472.3
32.5°	464.6
33°	454.2
34°	433.8
35°	408.4
36°	380.3
37°	348.5
37.5°	333.7
38°	313.6
39°	277.8
40°	247.0
42.5°	171.0
45°	107.8



TEST NUMBER: P1249074  
CATALOG NUMBER: P3AS09R709027DE010 E3D1WH

**CANDELA DISTRIBUTION (continued):**

	0°
47.5°	57.9
50°	13.7
52.5°	1.7
55°	1.0
57.5°	1.0
60°	0.7
62.5°	0.7
65°	0.7
67.5°	0.3
70°	0.3
72.5°	0.3
75°	0.3
77.5°	0.3
80°	0.3
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)