

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1250254

Luminaire Tested: P3AS24R209027D010 E3CD1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1250254
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-8)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS24R209027D010 E3CD1MMS
Description: 3in Adjustable LED luminaire with, R20 optic, 2700K CCT AND, 90CRI , E3CD1MMS TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2283.0 lumens
Efficiency: N/A
Efficacy: 79.3 lumens/watt
Spacing Criteria (0/90/45): 0.35 / 0.35 / 0.34
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1250254
CATALOG NUMBER: P3AS24R209027D010 E3CD1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P1250254
 CATALOG NUMBER: P3AS24R209027D010 E3CD1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	116	114	112	110	113	112	110	109	108	106	105	104	103	102	101	100	99	98	98	98	98
2	112	109	107	104	110	108	105	103	104	103	101	102	100	99	99	98	97	97	97	97	95
3	109	105	102	100	108	104	101	99	102	99	97	99	98	96	97	96	95	95	95	95	93
4	107	102	99	96	105	101	98	96	99	97	95	97	95	93	96	94	92	92	92	92	91
5	104	99	96	93	103	98	95	93	97	94	92	95	93	91	94	92	91	91	91	91	90
6	102	97	93	91	101	96	93	90	95	92	90	94	91	89	93	90	89	89	89	89	88
7	100	94	91	88	99	94	91	88	93	90	88	92	89	87	91	89	87	87	87	87	86
8	98	92	89	86	97	92	89	86	91	88	86	90	88	86	89	87	85	85	85	85	85
9	96	90	87	85	95	90	87	85	89	86	84	89	86	84	88	86	84	84	84	84	83
10	94	89	85	83	93	88	85	83	88	85	83	87	84	83	87	84	82	82	82	82	82

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3545769
5°	3077606
10°	1901635
15°	660481
20°	202831
25°	71714
30°	26536
35°	10654
40°	5696
45°	2233
50°	1228
55°	1376
60°	1579
65°	934
70°	1154
75°	1525
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2233 cd/sqm



TEST NUMBER: P1250254
 CATALOG NUMBER: P3AS24R209027D010 E3CD1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1160.4	50.8
10°-20°	920.7	40.3
20°-30°	159.4	7.0
30°-40°	29.0	1.3
40°-50°	6.6	0.3
50°-60°	3.2	0.1
60°-70°	2.0	0.1
70°-80°	1.7	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2240.5	98.1
0°-40°	2269.4	99.4
0°-60°	2279.3	99.8
0°-90°	2283.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2283.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	16170	
5°	13982	###
15°	2909	921
25°	296	159
35°	40	29
45°	7	7
55°	4	3
65°	2	2
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P1250254
CATALOG NUMBER: P3AS24R209027D010 E3CD1MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	16170.0
1°	16092.3
2°	15785.0
3°	15291.7
4°	14713.4
5°	13981.6
6°	13143.1
7°	12167.2
8°	11055.9
9°	9807.1
10°	8540.4
12.5°	5387.0
15°	2909.4
17.5°	1554.1
20°	869.2
22.5°	497.0
25°	296.4
27.5°	180.7
30°	104.8
32.5°	61.4
35°	39.8
37.5°	27.1
40°	19.9
42.5°	12.6
45°	7.2
47.5°	3.6
50°	3.6
52.5°	3.6
55°	3.6
57.5°	3.6
60°	3.6
62.5°	1.8
65°	1.8
67.5°	1.8
70°	1.8
72.5°	1.8
75°	1.8
77.5°	1.8
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)