

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1250257

Luminaire Tested: P3AS24R209027D010 E3D1LI

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1250257
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-8)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS24R209027D010 E3D1LI
Description: 3in Adjustable LED luminaire with, R20 optic, 2700K CCT AND, 90CRI , E3D1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2266.0 lumens
Efficiency: N/A
Efficacy: 78.7 lumens/watt
Spacing Criteria (0/90/45): 0.35 / 0.35 / 0.34
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1250257

CATALOG NUMBER: P3AS24R209027D010 E3D1LI

Luminous Intensity Polar Plot



TEST NUMBER: P1250257

CATALOG NUMBER: P3AS24R209027D010 E3D1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	114	112	110	113	111	110	108	107	106	105		104	103	102		100
2	112	109	106	104	110	107	105	103	104	102	101		101	100	98		99
3	109	105	102	99	107	104	101	98	101	99	97		99	97	95		97
4	106	101	98	95	105	100	97	95	99	96	94		97	95	93		95
5	104	98	95	92	102	98	94	92	96	93	91		95	92	90		93
6	101	96	92	89	100	95	92	89	94	91	89		93	90	88		92
7	99	93	90	87	98	93	89	87	92	89	86		91	88	86		90
8	97	91	87	85	96	91	87	85	90	87	85		89	86	84		88
9	95	89	85	83	94	89	85	83	88	85	83		87	84	83		87
10	93	87	84	81	92	87	83	81	86	83	81		86	83	81		85

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3437334
5°	2894071
10°	1807626
15°	675804
20°	231977
25°	96683
30°	45551
35°	20398
40°	9647
45°	4931
50°	1808
55°	344
60°	395
65°	467
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4931 cd/sqm

TEST NUMBER: P1250257

CATALOG NUMBER: P3AS24R209027D010 E3D1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1093.4	48.3
10°-20°	900.6	39.7
20°-30°	204.7	9.0
30°-40°	52.1	2.3
40°-50°	13.1	0.6
50°-60°	1.7	0.1
60°-70°	0.6	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2198.6	97.0
0°-40°	2250.7	99.3
0°-60°	2265.5	100.0
0°-90°	2266.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2266.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	15676	
5°	13148	###
15°	2977	901
25°	400	205
35°	76	52
45°	16	13
55°	1	2
65°	1	1
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1250257

CATALOG NUMBER: P3AS24R209027D010 E3D1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	15675.5
1°	15542.6
2°	15151.0
3°	14589.3
4°	13900.0
5°	13147.8
6°	12309.7
7°	11384.8
8°	10305.6
9°	9236.3
10°	8118.2
11°	6928.3
12°	5740.2
13°	4733.8
14°	3771.6
15°	2976.9
16°	2349.6
17°	1853.5
18°	1489.3
19°	1211.1
20°	994.1
21°	831.0
22°	693.7
23°	576.8
24°	481.1
25°	399.6
27.5°	261.4
30°	179.9
32.5°	110.7
35°	76.2
37.5°	48.7
40°	33.7
42.5°	23.0
45°	15.9
47.5°	10.6
50°	5.3
52.5°	2.7
55°	0.9
57.5°	0.9
60°	0.9
62.5°	0.9
65°	0.9
67.5°	0.0
70°	0.0
72.5°	0.0

TEST NUMBER: P1250257
CATALOG NUMBER: P3AS24R209027D010 E3D1LI

CANDELA DISTRIBUTION (continued):

	0°
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)