

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1250266

Luminaire Tested: P3AS24R209027D010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1250266
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-6)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS24R209027D010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R20 optic, 2700K CCT AND, 90CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 698.0 lumens
Efficiency: N/A
Efficacy: 24.2 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1250266

CATALOG NUMBER: P3AS24R209027D010 E3DLD1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1250266

CATALOG NUMBER: P3AS24R209027D010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	109	106	104	110	107	105	102	103	101	99		99	98	96		96
2	106	100	96	92	104	99	94	91	95	92	89		92	89	87		90
3	100	93	87	82	98	91	86	82	88	84	80		86	82	79		84
4	94	86	79	75	92	85	79	74	82	77	73		80	76	72		78
5	89	80	73	68	87	79	73	68	77	71	67		75	70	67		73
6	84	74	68	63	82	73	67	63	72	66	62		70	65	62		69
7	80	69	63	58	78	69	62	58	67	62	58		66	61	57		65
8	75	65	59	54	74	64	58	54	63	58	54		62	57	53		61
9	72	61	55	50	70	61	55	50	60	54	50		59	54	50		58
10	68	58	51	47	67	57	51	47	56	51	47		56	51	47		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	172662
5°	168038
10°	154595
15°	136073
20°	116700
25°	98038
30°	79253
35°	60284
40°	42880
45°	28313
50°	17535
55°	11507
60°	10482
65°	9651
70°	9104
75°	8303
80°	7829
85°	6793

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 28313 cd/sqm

TEST NUMBER: P1250266

CATALOG NUMBER: P3AS24R209027D010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	70.6	10.1
10°-20°	166.9	23.9
20°-30°	185.2	26.5
30°-40°	141.3	20.2
40°-50°	72.3	10.4
50°-60°	29.7	4.3
60°-70°	18.5	2.7
70°-80°	10.4	1.5
80°-90°	3.0	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	422.7	60.6
0°-40°	564.0	80.8
0°-60°	666.0	95.4
0°-90°	698.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	698.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	787	
5°	763	71
15°	599	167
25°	405	185
35°	225	141
45°	91	72
55°	30	30
65°	19	19
75°	10	10
85°	3	3
90°	0	

TEST NUMBER: P1250266

CATALOG NUMBER: P3AS24R209027D010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	787.4
1°	788.2
2°	784.7
3°	780.3
4°	773.2
5°	763.4
6°	751.9
7°	739.5
8°	726.2
9°	710.2
10°	694.3
12.5°	648.1
15°	599.4
17.5°	549.7
20°	500.1
22.5°	450.4
25°	405.2
27.5°	360.0
30°	313.0
32.5°	268.7
35°	225.2
37.5°	187.1
40°	149.8
42.5°	117.9
45°	91.3
47.5°	69.2
50°	51.4
52.5°	38.1
55°	30.1
57.5°	27.5
60°	23.9
62.5°	21.3
65°	18.6
67.5°	16.0
70°	14.2
72.5°	11.5
75°	9.8
77.5°	8.0
80°	6.2
82.5°	4.4
85°	2.7
87.5°	0.9
90°	0.0

(END OF REPORT)