

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1249195

Luminaire Tested: P3AS13R209027DE010 E3DL1GPH

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1249195  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-7)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R209027DE010 E3DL1GPH  
Description: 3in Adjustable LED luminaire with, R20 optic, 2700K CCT AND, 90CRI , E3DL1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 460.0 lumens  
Efficiency: N/A  
Efficacy: 31.5 lumens/watt  
Spacing Criteria (0/90/45): 0.44 / 0.44 / 0.46  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 14.6  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1249195  
CATALOG NUMBER: P3AS13R209027DE010 E3DL1GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P1249195  
 CATALOG NUMBER: P3AS13R209027DE010 E3DL1GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	95	95
2	110	106	102	100	108	104	101	98	101	98	96	98	96	94	95	94	92	91	91	91	91
3	106	100	96	93	104	99	95	92	97	93	91	94	92	89	92	90	88	87	87	87	87
4	102	96	91	88	100	95	90	87	92	89	86	91	88	85	89	86	84	83	83	83	83
5	98	91	87	83	97	90	86	83	89	85	82	87	84	81	86	83	81	79	79	79	79
6	95	87	83	79	93	87	82	79	85	81	78	84	81	78	83	80	77	76	76	76	76
7	91	84	79	76	90	83	79	76	82	78	75	81	78	75	80	77	75	73	73	73	73
8	88	81	76	73	87	80	76	73	79	75	72	78	75	72	78	74	72	71	71	71	71
9	85	78	73	70	85	77	73	70	77	73	70	76	72	69	75	72	69	68	68	68	68
10	83	75	71	68	82	75	70	67	74	70	67	73	70	67	73	69	67	66	66	66	66

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	353919
5°	321725
10°	237760
15°	147084
20°	83984
25°	47954
30°	26890
35°	14643
40°	8015
45°	4404
50°	2593
55°	1873
60°	1754
65°	1608
70°	1410
75°	1525
80°	1137
85°	1006

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 4404 cd/sqm



TEST NUMBER: P1249195  
 CATALOG NUMBER: P3AS13R209027DE010 E3DL1GPH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	126.6	27.5
10°-20°	180.7	39.3
20°-30°	94.3	20.5
30°-40°	36.5	7.9
40°-50°	11.8	2.6
50°-60°	4.7	1.0
60°-70°	3.1	0.7
70°-80°	1.8	0.4
80°-90°	0.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	401.5	87.3
0°-40°	438.0	95.2
0°-60°	454.5	98.8
0°-90°	460.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	460.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1614	
5°	1462	127
15°	648	181
25°	198	94
35°	55	36
45°	14	12
55°	5	5
65°	3	3
75°	2	2
85°	0	1
90°	0	



TEST NUMBER: P1249195  
CATALOG NUMBER: P3AS13R209027DE010 E3DL1GPH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1614.0
1°	1610.9
2°	1591.8
3°	1562.4
4°	1517.1
5°	1461.6
6°	1395.8
7°	1322.9
8°	1238.5
9°	1156.3
10°	1067.8
12.5°	848.8
15°	647.9
17.5°	484.8
20°	359.9
22.5°	266.6
25°	198.2
27.5°	146.2
30°	106.2
32.5°	76.9
35°	54.7
37.5°	39.5
40°	28.0
42.5°	20.0
45°	14.2
47.5°	10.2
50°	7.6
52.5°	5.8
55°	4.9
57.5°	4.4
60°	4.0
62.5°	3.6
65°	3.1
67.5°	2.7
70°	2.2
72.5°	2.2
75°	1.8
77.5°	1.3
80°	0.9
82.5°	0.9
85°	0.4
87.5°	0.4
90°	0.0

(END OF REPORT)