

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1250267

Luminaire Tested: P3AS24R209027D010 E3DLD1H

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1250267
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-6)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS24R209027D010 E3DLD1H
Description: 3in Adjustable LED luminaire with, R20 optic, 2700K CCT AND, 90CRI , E3DLD1H TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1423.0 lumens
Efficiency: N/A
Efficacy: 49.4 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1250267

CATALOG NUMBER: P3AS24R209027D010 E3DLD1H

Luminous Intensity Polar Plot



TEST NUMBER: P1250267

CATALOG NUMBER: P3AS24R209027D010 E3DLD1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	109	106	104	110	107	105	102	103	101	99	99	98	96	96	95	93	91		
2	106	100	96	92	104	99	94	91	95	92	89	92	89	87	90	87	85	83		
3	100	93	87	82	98	91	86	82	88	84	80	86	82	79	84	81	78	76		
4	94	86	79	75	92	85	79	74	82	77	73	80	76	72	78	75	72	70		
5	89	80	73	68	87	79	73	68	77	71	67	75	70	67	73	69	66	65		
6	84	74	68	63	82	73	67	63	72	66	62	70	65	62	69	65	61	60		
7	80	69	63	58	78	69	62	58	67	62	58	66	61	57	65	60	57	55		
8	75	65	59	54	74	64	58	54	63	58	54	62	57	53	61	57	53	52		
9	72	61	55	50	70	61	55	50	60	54	50	59	54	50	58	53	50	48		
10	68	58	51	47	67	57	51	47	56	51	47	56	51	47	55	50	47	45		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	351989
5°	342592
10°	315158
15°	277391
20°	237904
25°	199874
30°	161569
35°	122898
40°	87450
45°	57742
50°	35751
55°	23512
60°	21402
65°	19717
70°	18529
75°	16860
80°	16037
85°	13586

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 57742 cd/sqm

TEST NUMBER: P1250267

CATALOG NUMBER: P3AS24R209027D010 E3DLD1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	144.0	10.1
10°-20°	340.2	23.9
20°-30°	377.6	26.5
30°-40°	288.0	20.2
40°-50°	147.5	10.4
50°-60°	60.6	4.3
60°-70°	37.8	2.7
70°-80°	21.2	1.5
80°-90°	6.1	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	861.8	60.6
0°-40°	1149.8	80.8
0°-60°	1357.9	95.4
0°-90°	1423.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1423.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1605	
5°	1556	144
15°	1222	340
25°	826	378
35°	459	288
45°	186	147
55°	62	61
65°	38	38
75°	20	21
85°	5	6
90°	0	

TEST NUMBER: P1250267

CATALOG NUMBER: P3AS24R209027D010 E3DLD1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	1605.2
1°	1607.0
2°	1599.7
3°	1590.7
4°	1576.2
5°	1556.4
6°	1532.9
7°	1507.5
8°	1480.4
9°	1447.9
10°	1415.4
12.5°	1321.4
15°	1221.9
17.5°	1120.7
20°	1019.5
22.5°	918.3
25°	826.1
27.5°	733.9
30°	638.1
32.5°	547.7
35°	459.1
37.5°	381.4
40°	305.5
42.5°	240.4
45°	186.2
47.5°	141.0
50°	104.8
52.5°	77.7
55°	61.5
57.5°	56.0
60°	48.8
62.5°	43.4
65°	38.0
67.5°	32.5
70°	28.9
72.5°	23.5
75°	19.9
77.5°	16.3
80°	12.7
82.5°	9.0
85°	5.4
87.5°	1.8
90°	0.0

(END OF REPORT)