

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1250284

Luminaire Tested: P3AS24R259027D010 E3D1MW

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1250284  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-12)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS24R259027D010 E3D1MW  
Description: 3in Adjustable LED luminaire with, R25 optic, 2700K CCT AND, 90CRI , E3D1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2301.0 lumens  
Efficiency: N/A  
Efficacy: 79.9 lumens/watt  
Spacing Criteria (0/90/45): 0.45 / 0.45 / 0.41  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 28.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1250284  
CATALOG NUMBER: P3AS24R259027D010 E3D1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P1250284  
 CATALOG NUMBER: P3AS24R259027D010 E3D1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	99	100
1	115	113	111	110	113	111	109	108	107	106	105	103	103	102	100	99	99	97	97	97	97
2	112	108	105	103	110	107	104	102	104	102	100	101	99	98	98	97	96	96	96	96	94
3	108	104	101	98	107	103	100	97	100	98	96	98	96	94	96	94	93	92	92	92	92
4	105	100	97	94	104	99	96	93	97	95	92	96	93	91	94	92	90	89	89	89	89
5	103	97	93	90	101	96	93	90	95	92	89	93	91	89	92	90	88	87	87	87	87
6	100	94	90	87	99	93	90	87	92	89	87	91	88	86	90	87	86	85	85	85	85
7	97	91	88	85	96	91	87	85	90	87	84	89	86	84	88	85	83	83	83	83	83
8	95	89	85	83	94	89	85	82	88	84	82	87	84	82	86	83	81	81	81	81	81
9	93	87	83	80	92	86	83	80	86	82	80	85	82	80	84	82	80	79	79	79	79
10	91	85	81	78	90	84	81	78	84	80	78	83	80	78	82	80	78	77	77	77	77

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	2460110
5°	2281680
10°	1769484
15°	887270
20°	291505
25°	115918
30°	43475
35°	12582
40°	5696
45°	2233
50°	1842
55°	1376
60°	1579
65°	1868
70°	1154
75°	1525
80°	2273
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 80°  
 Luminance: 2273 cd/sqm



TEST NUMBER: P1250284  
 CATALOG NUMBER: P3AS24R259027D010 E3D1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	911.7	39.6
10°-20°	1087.8	47.3
20°-30°	245.2	10.7
30°-40°	39.7	1.7
40°-50°	7.2	0.3
50°-60°	3.8	0.2
60°-70°	3.3	0.1
70°-80°	1.9	0.1
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2244.7	97.6
0°-40°	2284.5	99.3
0°-60°	2295.5	99.8
0°-90°	2301.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2301.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	11219	
5°	10366	912
15°	3908	1088
25°	479	245
35°	47	40
45°	7	7
55°	4	4
65°	4	3
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P1250284  
CATALOG NUMBER: P3AS24R259027D010 E3D1MW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	11219.0
1°	11200.9
2°	11110.5
3°	10944.2
4°	10692.9
5°	10365.7
6°	9975.2
7°	9552.2
8°	9067.7
9°	8538.1
10°	7946.9
11°	7265.4
12°	6480.8
13°	5660.1
14°	4779.7
15°	3908.4
17.5°	2227.2
20°	1249.2
22.5°	753.8
25°	479.1
27.5°	294.7
30°	171.7
32.5°	90.4
35°	47.0
37.5°	30.7
40°	19.9
42.5°	12.7
45°	7.2
47.5°	5.4
50°	5.4
52.5°	5.4
55°	3.6
57.5°	3.6
60°	3.6
62.5°	3.6
65°	3.6
67.5°	3.6
70°	1.8
72.5°	1.8
75°	1.8
77.5°	1.8
80°	1.8
82.5°	0.0
85°	0.0
87.5°	0.0



TEST NUMBER: P1250284  
CATALOG NUMBER: P3AS24R259027D010 E3D1MW

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)