

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1249199

Luminaire Tested: P3AS13R209027DE010 E3DL1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1249199
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-7)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R209027DE010 E3DL1WMH
Description: 3in Adjustable LED luminaire with, R20 optic, 2700K CCT AND, 90CRI , E3DL1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 939.0 lumens
Efficiency: N/A
Efficacy: 64.3 lumens/watt
Spacing Criteria (0/90/45): 0.44 / 0.44 / 0.46
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1249199

CATALOG NUMBER: P3AS13R209027DE010 E3DL1WMH

Luminous Intensity Polar Plot





TEST NUMBER: P1249199

CATALOG NUMBER: P3AS13R209027DE010 E3DL1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99	98	97	95
2	110	106	102	100	108	104	101	98	101	98	96		98	96	94		95	94	92	91
3	106	100	96	93	104	99	95	92	97	93	91		94	92	89		92	90	88	87
4	102	96	91	88	100	95	90	87	92	89	86		91	88	85		89	86	84	83
5	98	91	87	83	97	90	86	83	89	85	82		87	84	81		86	83	81	79
6	95	87	83	79	93	87	82	79	85	81	78		84	81	78		83	80	77	76
7	91	84	79	76	90	83	79	76	82	78	75		81	78	75		80	77	75	73
8	88	81	76	73	87	80	76	73	79	75	72		78	75	72		78	74	72	71
9	85	78	73	70	85	77	73	70	77	73	70		76	72	69		75	72	69	68
10	83	75	71	68	82	75	70	67	74	70	67		73	70	67		73	69	67	66

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	722464
5°	656723
10°	485362
15°	300251
20°	171468
25°	97893
30°	54895
35°	29874
40°	16345
45°	8993
50°	5254
55°	3823
60°	3596
65°	3269
70°	2885
75°	3050
80°	2273
85°	2264

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 8993 cd/sqm

TEST NUMBER: P1249199

CATALOG NUMBER: P3AS13R209027DE010 E3DL1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	258.4	27.5
10°-20°	368.8	39.3
20°-30°	192.5	20.5
30°-40°	74.4	7.9
40°-50°	24.1	2.6
50°-60°	9.5	1.0
60°-70°	6.3	0.7
70°-80°	3.7	0.4
80°-90°	1.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	819.7	87.3
0°-40°	894.1	95.2
0°-60°	927.8	98.8
0°-90°	939.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	939.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3295	
5°	2984	258
15°	1323	369
25°	405	193
35°	112	74
45°	29	24
55°	10	10
65°	6	6
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1249199

CATALOG NUMBER: P3AS13R209027DE010 E3DL1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	3294.7
1°	3288.3
2°	3249.3
3°	3189.4
4°	3096.9
5°	2983.5
6°	2849.3
7°	2700.5
8°	2528.1
9°	2360.3
10°	2179.8
12.5°	1732.6
15°	1322.6
17.5°	989.7
20°	734.8
22.5°	544.3
25°	404.6
27.5°	298.4
30°	216.8
32.5°	156.9
35°	111.6
37.5°	80.7
40°	57.1
42.5°	40.8
45°	29.0
47.5°	20.9
50°	15.4
52.5°	11.8
55°	10.0
57.5°	9.1
60°	8.2
62.5°	7.3
65°	6.3
67.5°	5.4
70°	4.5
72.5°	4.5
75°	3.6
77.5°	2.7
80°	1.8
82.5°	1.8
85°	0.9
87.5°	0.9
90°	0.0

(END OF REPORT)