

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1249211

Luminaire Tested: P3AS13R259027DE010 E3CB1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1249211
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-12)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R259027DE010 E3CB1MMS
Description: 3in Adjustable LED luminaire with, R25 optic, 2700K CCT AND, 90CRI , E3CB1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1155.0 lumens
Efficiency: N/A
Efficacy: 79.1 lumens/watt
Spacing Criteria (0/90/45): 0.45 / 0.45 / 0.41
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1249211

CATALOG NUMBER: P3AS13R259027DE010 E3CB1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1249211

CATALOG NUMBER: P3AS13R259027DE010 E3CB1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	113	111	110	113	111	109	108	107	106	105		103	103	102		100
2	112	108	105	103	110	107	104	102	104	102	100		101	99	98		98
3	108	104	101	98	107	103	100	97	100	98	96		98	96	94		96
4	105	100	97	94	104	99	96	93	97	95	92		96	93	91		94
5	103	97	93	90	101	96	93	90	95	92	89		93	91	89		92
6	100	94	90	87	99	93	90	87	92	89	87		91	88	86		90
7	97	91	88	85	96	91	87	85	90	87	84		89	86	84		88
8	95	89	85	83	94	89	85	82	88	84	82		87	84	82		86
9	93	87	83	80	92	86	83	80	86	82	80		85	82	80		84
10	91	85	81	78	90	84	81	78	84	80	78		83	80	78		82

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1234857
5°	1145297
10°	888204
15°	445360
20°	146313
25°	58189
30°	21826
35°	6318
40°	2863
45°	1116
50°	921
55°	688
60°	789
65°	934
70°	577
75°	763
80°	1137
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 80°

Luminance: 1137 cd/sqm

TEST NUMBER: P1249211

CATALOG NUMBER: P3AS13R259027DE010 E3CB1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	457.7	39.6
10°-20°	546.0	47.3
20°-30°	123.1	10.7
30°-40°	20.0	1.7
40°-50°	3.6	0.3
50°-60°	1.9	0.2
60°-70°	1.7	0.1
70°-80°	1.0	0.1
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1126.7	97.6
0°-40°	1146.7	99.3
0°-60°	1152.2	99.8
0°-90°	1155.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1155.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5631	
5°	5203	458
15°	1962	546
25°	240	123
35°	24	20
45°	4	4
55°	2	2
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1249211

CATALOG NUMBER: P3AS13R259027DE010 E3CB1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	5631.4
1°	5622.3
2°	5577.0
3°	5493.5
4°	5367.4
5°	5203.1
6°	5007.1
7°	4794.8
8°	4551.6
9°	4285.7
10°	3989.0
11°	3646.9
12°	3253.1
13°	2841.1
14°	2399.2
15°	1961.8
17.5°	1117.9
20°	627.0
22.5°	378.4
25°	240.5
27.5°	147.9
30°	86.2
32.5°	45.4
35°	23.6
37.5°	15.4
40°	10.0
42.5°	6.4
45°	3.6
47.5°	2.7
50°	2.7
52.5°	2.7
55°	1.8
57.5°	1.8
60°	1.8
62.5°	1.8
65°	1.8
67.5°	1.8
70°	0.9
72.5°	0.9
75°	0.9
77.5°	0.9
80°	0.9
82.5°	0.0
85°	0.0
87.5°	0.0



TEST NUMBER: P1249211
CATALOG NUMBER: P3AS13R259027DE010 E3CB1MMS

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)