

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1250312

Luminaire Tested: P3AS24R309027D010 E3CD1MMS

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1250312  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-16)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS24R309027D010 E3CD1MMS  
Description: 3in Adjustable LED luminaire with, R30 optic, 2700K CCT AND, 90CRI , E3CD1MMS TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2300.9 lumens  
Efficiency: N/A  
Efficacy: 79.9 lumens/watt  
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.47  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 28.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1250312

CATALOG NUMBER: P3AS24R309027D010 E3CD1MMS

### Luminous Intensity Polar Plot





TEST NUMBER: P1250312

CATALOG NUMBER: P3AS24R309027D010 E3CD1MMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |  |     |     |     |     |  |     |     |     |  |     |     |     |  |     |     |     |
|-----|-----|-----|-----|-----|--|-----|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|
| RF  | 20  |     |     |     |  | 20  |     |     |     |  | 20  |     |     |  |     | 20  |     |  |     |     | 20  |
| RC  | 80  |     |     |     |  | 70  |     |     |     |  | 30  |     |     |  |     | 10  |     |  |     |     | 0   |
| RW  | 70  | 50  | 30  | 10  |  | 70  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  |
| RCR |     |     |     |     |  |     |     |     |     |  |     |     |     |  |     |     |     |  |     |     |     |
| 0   | 119 | 119 | 119 | 119 |  | 116 | 116 | 116 | 116 |  | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 | 102 | 102 |
| 1   | 115 | 113 | 111 | 109 |  | 113 | 111 | 109 | 108 |  | 107 | 106 | 104 |  | 103 | 102 | 101 |  | 100 | 99  | 98  |
| 2   | 111 | 108 | 105 | 102 |  | 109 | 106 | 104 | 101 |  | 103 | 101 | 99  |  | 100 | 99  | 97  |  | 98  | 96  | 95  |
| 3   | 108 | 103 | 100 | 97  |  | 106 | 102 | 99  | 96  |  | 100 | 97  | 95  |  | 97  | 95  | 93  |  | 95  | 94  | 92  |
| 4   | 105 | 100 | 96  | 93  |  | 103 | 99  | 95  | 92  |  | 97  | 94  | 91  |  | 95  | 92  | 90  |  | 93  | 91  | 89  |
| 5   | 102 | 96  | 92  | 89  |  | 100 | 95  | 91  | 89  |  | 94  | 90  | 88  |  | 92  | 89  | 87  |  | 91  | 88  | 87  |
| 6   | 99  | 93  | 89  | 86  |  | 98  | 92  | 88  | 86  |  | 91  | 88  | 85  |  | 90  | 87  | 85  |  | 89  | 86  | 84  |
| 7   | 96  | 90  | 86  | 83  |  | 95  | 89  | 86  | 83  |  | 88  | 85  | 82  |  | 87  | 84  | 82  |  | 86  | 84  | 82  |
| 8   | 94  | 87  | 83  | 81  |  | 93  | 87  | 83  | 80  |  | 86  | 83  | 80  |  | 85  | 82  | 80  |  | 84  | 82  | 80  |
| 9   | 91  | 85  | 81  | 78  |  | 90  | 84  | 81  | 78  |  | 84  | 80  | 78  |  | 83  | 80  | 78  |  | 82  | 79  | 77  |
| 10  | 89  | 83  | 79  | 76  |  | 88  | 82  | 78  | 76  |  | 82  | 78  | 76  |  | 81  | 78  | 76  |  | 80  | 77  | 75  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |         |
|-----|---------|
|     | 0°      |
| 0°  | 1873797 |
| 5°  | 1838384 |
| 10° | 1627425 |
| 15° | 1031084 |
| 20° | 391381  |
| 25° | 115870  |
| 30° | 45754   |
| 35° | 14027   |
| 40° | 6212    |
| 45° | 2233    |
| 50° | 1842    |
| 55° | 1376    |
| 60° | 1579    |
| 65° | 1868    |
| 70° | 1154    |
| 75° | 1525    |
| 80° | 2273    |
| 85° | 0       |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
Vertical Angle: 80°  
Luminance: 2273 cd/sqm

TEST NUMBER: P1250312

CATALOG NUMBER: P3AS24R309027D010 E3CD1MMS

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 767.8  | 33.4      |
| 10°-20°   | 1196.5 | 52.0      |
| 20°-30°   | 277.8  | 12.1      |
| 30°-40°   | 43.0   | 1.9       |
| 40°-50°   | 7.4    | 0.3       |
| 50°-60°   | 3.4    | 0.1       |
| 60°-70°   | 2.9    | 0.1       |
| 70°-80°   | 1.9    | 0.1       |
| 80°-90°   | 0.2    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 2242.1 | 97.4      |
| 0°-40°    | 2285.1 | 99.3      |
| 0°-60°    | 2295.9 | 99.8      |
| 0°-90°    | 2300.9 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 2300.9 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 8545 |      |
| 5°  | 8352 | 768  |
| 15° | 4542 | 1197 |
| 25° | 479  | 278  |
| 35° | 52   | 43   |
| 45° | 7    | 7    |
| 55° | 4    | 3    |
| 65° | 4    | 3    |
| 75° | 2    | 2    |
| 85° | 0    | 0    |
| 90° | 0    |      |

TEST NUMBER: P1250312

CATALOG NUMBER: P3AS24R309027D010 E3CD1MMS


**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 8545.2 |
| 1°    | 8539.7 |
| 2°    | 8516.2 |
| 3°    | 8476.5 |
| 4°    | 8425.9 |
| 5°    | 8351.8 |
| 6°    | 8259.6 |
| 7°    | 8122.2 |
| 8°    | 7934.3 |
| 9°    | 7657.8 |
| 10°   | 7308.9 |
| 11°   | 6858.9 |
| 12°   | 6351.0 |
| 13°   | 5787.1 |
| 14°   | 5167.2 |
| 15°   | 4541.9 |
| 17.5° | 2971.3 |
| 20°   | 1677.2 |
| 22.5° | 856.7  |
| 25°   | 478.9  |
| 27.5° | 294.6  |
| 30°   | 180.7  |
| 32.5° | 97.6   |
| 35°   | 52.4   |
| 37.5° | 34.3   |
| 40°   | 21.7   |
| 42.5° | 12.7   |
| 45°   | 7.2    |
| 47.5° | 5.4    |
| 50°   | 5.4    |
| 52.5° | 3.6    |
| 55°   | 3.6    |
| 57.5° | 3.6    |
| 60°   | 3.6    |
| 62.5° | 3.6    |
| 65°   | 3.6    |
| 67.5° | 1.8    |
| 70°   | 1.8    |
| 72.5° | 1.8    |
| 75°   | 1.8    |
| 77.5° | 1.8    |
| 80°   | 1.8    |
| 82.5° | 0.0    |
| 85°   | 0.0    |
| 87.5° | 0.0    |



TEST NUMBER: P1250312  
CATALOG NUMBER: P3AS24R309027D010 E3CD1MMS

CANDELA DISTRIBUTION (continued):



(END OF REPORT)