

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1249264

Luminaire Tested: P3AS13R309027DE010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1249264
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-14)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R309027DE010 E3DLD1WMH
Description: 3in Adjustable LED luminaire with, R30 optic, 2700K CCT AND, 90CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 739.0 lumens
Efficiency: N/A
Efficacy: 50.6 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1249264

CATALOG NUMBER: P3AS13R309027DE010 E3DLD1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1249264

CATALOG NUMBER: P3AS13R309027DE010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	105	102	103	101	99		99	98	96		96
2	106	100	96	92	104	99	94	91	95	92	89		92	89	87		89
3	100	92	87	82	98	91	86	82	88	84	80		86	82	79		84
4	94	85	79	74	92	84	79	74	82	77	73		80	76	72		78
5	89	79	73	68	87	78	72	68	76	71	67		75	70	66		73
6	84	74	67	62	82	73	67	62	71	66	62		70	65	61		69
7	79	69	62	58	78	68	62	58	67	61	57		66	61	57		65
8	75	65	58	54	74	64	58	53	63	57	53		62	57	53		61
9	71	61	54	50	70	60	54	50	59	54	50		58	53	50		57
10	68	57	51	47	67	57	51	47	56	50	47		55	50	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	174591
5°	170658
10°	158714
15°	141227
20°	121461
25°	102901
30°	85406
35°	67003
40°	48033
45°	31507
50°	17944
55°	11775
60°	11139
65°	10377
70°	9296
75°	8472
80°	7956
85°	6793

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 31507 cd/sqm

TEST NUMBER: P1249264

CATALOG NUMBER: P3AS13R309027DE010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	72.0	9.7
10°-20°	172.9	23.4
20°-30°	194.9	26.4
30°-40°	155.6	21.1
40°-50°	80.0	10.8
50°-60°	30.1	4.1
60°-70°	19.7	2.7
70°-80°	10.7	1.4
80°-90°	3.1	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	439.8	59.5
0°-40°	595.5	80.6
0°-60°	705.6	95.5
0°-90°	739.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	739.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	796	
5°	775	72
15°	622	173
25°	425	195
35°	250	156
45°	102	80
55°	31	30
65°	20	20
75°	10	11
85°	3	3
90°	0	

TEST NUMBER: P1249264

CATALOG NUMBER: P3AS13R309027DE010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	796.2
1°	796.2
2°	793.5
3°	788.9
4°	782.6
5°	775.3
6°	766.3
7°	754.5
8°	741.8
9°	727.3
10°	712.8
11°	696.4
12°	679.2
13°	661.1
14°	642.0
15°	622.1
17.5°	571.3
20°	520.5
22.5°	471.5
25°	425.3
27.5°	380.0
30°	337.3
32.5°	293.8
35°	250.3
37.5°	207.7
40°	167.8
42.5°	132.4
45°	101.6
47.5°	75.3
50°	52.6
52.5°	37.2
55°	30.8
57.5°	28.1
60°	25.4
62.5°	22.7
65°	20.0
67.5°	17.2
70°	14.5
72.5°	11.8
75°	10.0
77.5°	8.2
80°	6.3
82.5°	4.5
85°	2.7
87.5°	0.9



TEST NUMBER: P1249264

CATALOG NUMBER: P3AS13R309027DE010 E3DLD1WMH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)