

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1250318

Luminaire Tested: P3AS24R309027D010 E3D1WMH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1250318
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-10)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS24R309027D010 E3D1WMH
Description: 3in Adjustable LED luminaire with, R30 optic, 2700K CCT AND, 90CRI , E3D1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2282.0 lumens
Efficiency: N/A
Efficacy: 79.2 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.47
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1250318

CATALOG NUMBER: P3AS24R309027D010 E3D1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1250318

CATALOG NUMBER: P3AS24R309027D010 E3D1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	98
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97	96	95
2	111	108	105	102	109	106	103	101	103	101	99	100	98	97	97	96	95	94	93	92
3	108	103	100	97	106	102	99	96	99	97	95	97	95	93	95	93	92	90	89	88
4	105	99	95	92	103	98	95	92	96	93	91	94	92	90	93	91	89	87	86	85
5	101	96	92	89	100	95	91	88	93	90	87	92	89	87	90	88	86	84	83	82
6	99	92	88	85	97	92	88	85	90	87	85	89	86	84	88	85	83	81	80	79
7	96	89	85	82	95	89	85	82	88	84	82	87	84	81	86	83	81	79	78	77
8	93	87	83	80	92	86	82	80	85	82	79	84	81	79	84	81	79	77	76	75
9	91	84	80	77	90	84	80	77	83	79	77	82	79	77	82	79	77	75	74	73
10	88	82	78	75	88	81	78	75	81	77	75	80	77	75	80	77	75	73	72	71

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1815622
5°	1791961
10°	1564545
15°	994444
20°	393994
25°	131596
30°	61225
35°	27733
40°	10649
45°	5210
50°	1501
55°	688
60°	395
65°	467
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 5210 cd/sqm

TEST NUMBER: P1250318

CATALOG NUMBER: P3AS24R309027D010 E3D1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	744.3	32.6
10°-20°	1154.2	50.6
20°-30°	297.6	13.0
30°-40°	69.9	3.1
40°-50°	13.6	0.6
50°-60°	1.6	0.1
60°-70°	0.8	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2196.1	96.2
0°-40°	2266.0	99.3
0°-60°	2281.2	100.0
0°-90°	2282.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2282.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8280	
5°	8141	744
15°	4380	1154
25°	544	298
35°	104	70
45°	17	14
55°	2	2
65°	1	1
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1250318

CATALOG NUMBER: P3AS24R309027D010 E3D1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	8279.9
1°	8273.7
2°	8254.2
3°	8232.1
4°	8199.3
5°	8140.9
6°	8046.1
7°	7888.4
8°	7673.1
9°	7392.3
10°	7026.5
11°	6591.5
12°	6116.7
13°	5570.2
14°	4997.9
15°	4380.5
16°	3775.4
17°	3192.6
18°	2633.6
19°	2120.7
20°	1688.4
21°	1328.8
22°	1045.3
23°	827.4
24°	662.6
25°	543.9
26°	453.5
27°	385.3
28°	333.1
29°	285.2
30°	241.8
32.5°	152.4
35°	103.6
37.5°	64.7
40°	37.2
42.5°	24.8
45°	16.8
47.5°	9.7
50°	4.4
52.5°	1.8
55°	1.8
57.5°	0.9
60°	0.9
62.5°	0.9
65°	0.9



TEST NUMBER: P1250318

CATALOG NUMBER: P3AS24R309027D010 E3D1WMH

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.9
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)