

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1249270

Luminaire Tested: P3AS13R309027DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1249270
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-13)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R309027DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R30 optic, 2700K CCT AND, 90CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 585.0 lumens
Efficiency: N/A
Efficacy: 40.1 lumens/watt
Spacing Criteria (0/90/45): 0.66 / 0.66 / 0.7
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1249270
CATALOG NUMBER: P3AS13R309027DE010 E3DLP1WMH

Luminous Intensity Polar Plot





TEST NUMBER: P1249270
 CATALOG NUMBER: P3AS13R309027DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86			
3	102	95	90	86	100	94	89	85	91	87	84	89	86	83	87	84	82	80			
4	97	89	84	79	95	88	83	79	86	81	78	84	80	77	82	79	76	74			
5	92	84	78	73	90	83	77	73	81	76	72	79	75	72	78	74	71	70			
6	88	79	73	68	86	78	72	68	76	71	68	75	71	67	74	70	67	65			
7	83	74	68	64	82	74	68	64	72	67	63	71	67	63	70	66	63	61			
8	80	70	64	60	78	70	64	60	69	63	60	67	63	60	67	62	59	58			
9	76	67	61	57	75	66	60	57	65	60	56	64	60	56	63	59	56	55			
10	73	63	58	54	72	63	57	54	62	57	54	61	57	53	61	56	53	52			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	199896
5°	193682
10°	174501
15°	144360
20°	111776
25°	83835
30°	60870
35°	40555
40°	24932
45°	14637
50°	8972
55°	7264
60°	6359
65°	5189
70°	4680
75°	4575
80°	3410
85°	4529

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 14637 cd/sqm



TEST NUMBER: P1249270
 CATALOG NUMBER: P3AS13R309027DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	80.9	13.8
10°-20°	175.1	29.9
20°-30°	159.3	27.2
30°-40°	96.3	16.5
40°-50°	38.6	6.6
50°-60°	17.1	2.9
60°-70°	10.3	1.8
70°-80°	5.6	1.0
80°-90°	1.6	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	415.4	71.0
0°-40°	511.7	87.5
0°-60°	567.5	97.0
0°-90°	585.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	585.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	912	
5°	880	81
15°	636	175
25°	346	159
35°	152	96
45°	47	39
55°	19	17
65°	10	10
75°	5	6
85°	2	2
90°	0	



TEST NUMBER: P1249270
CATALOG NUMBER: P3AS13R309027DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	911.6
1°	910.7
2°	907.1
3°	900.8
4°	891.7
5°	879.9
6°	865.4
7°	850.0
8°	830.0
9°	807.3
10°	783.7
11°	756.5
12°	727.5
13°	698.5
14°	666.7
15°	635.9
17.5°	555.1
20°	479.0
22.5°	408.2
25°	346.5
27.5°	290.3
30°	240.4
32.5°	194.1
35°	151.5
37.5°	116.1
40°	87.1
42.5°	63.5
45°	47.2
47.5°	35.4
50°	26.3
52.5°	20.9
55°	19.0
57.5°	16.3
60°	14.5
62.5°	11.8
65°	10.0
67.5°	9.1
70°	7.3
72.5°	6.3
75°	5.4
77.5°	4.5
80°	2.7
82.5°	1.8
85°	1.8
87.5°	0.9



TEST NUMBER: P1249270
CATALOG NUMBER: P3AS13R309027DE010 E3DLP1WMH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)