

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1249331

Luminaire Tested: P3AS13R459027DE010 E3CB1MB

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1249331
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-28)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R459027DE010 E3CB1MB
Description: 3in Adjustable LED luminaire with, R45 optic, 2700K CCT AND, 90CRI , E3CB1MB TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1216.9 lumens
Efficiency: N/A
Efficacy: 83.3 lumens/watt
Spacing Criteria (0/90/45): 0.72 / 0.72 / 0.66
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1249331
CATALOG NUMBER: P3AS13R459027DE010 E3CB1MB

Luminous Intensity Polar Plot





TEST NUMBER: P1249331
 CATALOG NUMBER: P3AS13R459027DE010 E3CB1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	95	95
2	110	106	102	100	108	104	101	98	101	98	96	98	96	94	95	94	92	91	91	91	91
3	106	100	96	93	104	99	95	92	96	93	91	94	91	89	92	90	88	87	87	87	87
4	102	95	91	87	100	94	90	87	92	89	86	90	87	85	88	86	84	83	83	83	83
5	98	91	86	82	96	90	85	82	88	84	81	87	83	81	85	82	80	79	79	79	79
6	94	87	82	78	93	86	81	78	85	80	77	83	80	77	82	79	76	75	75	75	75
7	90	83	78	74	89	82	78	74	81	77	74	80	76	74	79	76	73	72	72	72	72
8	87	79	74	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69	69	69	69
9	84	76	71	68	83	76	71	68	75	71	68	74	70	67	73	70	67	66	66	66	66
10	81	73	68	65	80	73	68	65	72	68	65	71	67	65	71	67	65	64	64	64	64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	527633
5°	530441
10°	514152
15°	430854
20°	329355
25°	200504
30°	83431
35°	26716
40°	8301
45°	1675
50°	1228
55°	1376
60°	1184
65°	1401
70°	1154
75°	1525
80°	1137
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1675 cd/sqm



TEST NUMBER: P1249331
 CATALOG NUMBER: P3AS13R459027DE010 E3CB1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	227.3	18.7
10°-20°	521.6	42.9
20°-30°	375.6	30.9
30°-40°	78.1	6.4
40°-50°	7.1	0.6
50°-60°	2.9	0.2
60°-70°	2.3	0.2
70°-80°	1.5	0.1
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1124.5	92.4
0°-40°	1202.6	98.8
0°-60°	1212.7	99.7
0°-90°	1216.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1216.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2406	
5°	2410	227
15°	1898	522
25°	829	376
35°	100	78
45°	5	7
55°	4	3
65°	3	2
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P1249331
CATALOG NUMBER: P3AS13R459027DE010 E3CB1MB

CANDELA DISTRIBUTION (FULL):

	0°
0°	2406.2
2.5°	2407.1
5°	2409.8
7.5°	2392.6
10°	2309.1
12.5°	2134.8
15°	1897.9
17.5°	1655.6
20°	1411.4
22.5°	1130.9
25°	828.7
27.5°	546.4
30°	329.5
32.5°	184.3
35°	99.8
37.5°	56.3
40°	29.0
42.5°	12.7
45°	5.4
47.5°	3.6
50°	3.6
52.5°	3.6
55°	3.6
57.5°	2.7
60°	2.7
62.5°	2.7
65°	2.7
67.5°	1.8
70°	1.8
72.5°	1.8
75°	1.8
77.5°	0.9
80°	0.9
82.5°	0.9
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)