

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1250398

Luminaire Tested: P3AS24R459027D010 E3CB1MMS

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1250398  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-28)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS24R459027D010 E3CB1MMS  
Description: 3in Adjustable LED luminaire with, R45 optic, 2700K CCT AND, 90CRI , E3CB1MMS TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2423.9 lumens  
Efficiency: N/A  
Efficacy: 84.2 lumens/watt  
Spacing Criteria (0/90/45): 0.72 / 0.72 / 0.66  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 28.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1250398  
CATALOG NUMBER: P3AS24R459027D010 E3CB1MMS

### Luminous Intensity Polar Plot





TEST NUMBER: P1250398

CATALOG NUMBER: P3AS24R459027D010 E3CB1MMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	95	95
2	110	106	102	100	108	104	101	98	101	98	96	98	96	94	95	94	92	91	91	91	91
3	106	100	96	93	104	99	95	92	96	93	91	94	91	89	92	90	88	87	87	87	87
4	102	95	91	87	100	94	90	87	92	89	86	90	87	85	88	86	84	82	82	82	82
5	98	91	86	82	96	90	85	82	88	84	81	87	83	81	85	82	80	79	79	79	79
6	94	87	82	78	93	86	81	78	85	80	77	83	80	77	82	79	76	75	75	75	75
7	90	83	78	74	89	82	78	74	81	77	74	80	76	74	79	76	73	72	72	72	72
8	87	79	74	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69	69	69	69
9	84	76	71	68	83	76	71	68	75	71	68	74	70	67	73	70	67	66	66	66	66
10	81	73	68	65	80	73	68	65	72	68	65	71	67	65	71	67	65	64	64	64	64

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1050946
5°	1056546
10°	1024074
15°	858166
20°	656004
25°	399362
30°	166177
35°	53244
40°	16574
45°	3349
50°	2456
55°	2753
60°	2368
65°	2802
70°	2308
75°	3050
80°	2273
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 3349 cd/sqm



TEST NUMBER: P1250398  
 CATALOG NUMBER: P3AS24R459027D010 E3CB1MMS

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	452.7	18.7
10°-20°	1039.0	42.9
20°-30°	748.1	30.9
30°-40°	155.6	6.4
40°-50°	14.2	0.6
50°-60°	5.8	0.2
60°-70°	4.7	0.2
70°-80°	3.1	0.1
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2239.7	92.4
0°-40°	2395.4	98.8
0°-60°	2415.4	99.6
0°-90°	2423.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2423.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4793	
5°	4800	453
15°	3780	1039
25°	1651	748
35°	199	156
45°	11	14
55°	7	6
65°	5	5
75°	4	3
85°	0	1
90°	0	



TEST NUMBER: P1250398  
CATALOG NUMBER: P3AS24R459027D010 E3CB1MMS

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	4792.7
2.5°	4794.5
5°	4799.9
7.5°	4765.5
10°	4599.2
12.5°	4252.1
15°	3780.2
17.5°	3297.5
20°	2811.2
22.5°	2252.6
25°	1650.6
27.5°	1088.3
30°	656.3
32.5°	367.0
35°	198.9
37.5°	112.1
40°	57.9
42.5°	25.3
45°	10.8
47.5°	7.2
50°	7.2
52.5°	7.2
55°	7.2
57.5°	5.4
60°	5.4
62.5°	5.4
65°	5.4
67.5°	3.6
70°	3.6
72.5°	3.6
75°	3.6
77.5°	1.8
80°	1.8
82.5°	1.8
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)